Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

	△数 COUNT	訂正事項 DESCRIPTION OF REVISIONS	擔當 BY	檢圖 CHKD	年月日 DATE
5	1	Released(RE-2-2440)	KYG	LHJ	23. 10. 26
6	-	EC(RE-2-2477)	KYG	LHJ	23. 12. 08
7	1	EC(RE-2-2556)	OSW	LHJ	24. 05. 01





















NO.	DESCRIPTIONS	MATERIAL	FINISH	REMARKS
7	GASKET	SILICONE	GRAY COLOR	-
6	BRACKET	STAINLESS STEEL	NICKEL PLATING	-
5	SHELL	STAINLESS STEEL	CLEANSING	-
4	MID PLATE	STAINLESS STEEL	NICKEL PLATING ⚠1	-
3	CONTACT 2ND	COPPER ALLOY	CONTACT AREA : GOLD OVER NICKEL PLATING SOLDER AREA : GOLD OVER NICKEL PLATING THE OTHER AREA : NICKEL PLATING	-
2	CONTACT 1ST	COPPER ALLOY		
1	INSERT CASE	THERMOPLASTIC	BLACK COLOR	UL94V-0

CODE NO. (OLD)

DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
Y.G.KIM 22.08.24	Y.G.KIM 22.08.24	H.J.LEE 22.08.24	H.J.LEE 22.08.24	ENG 24.05.01 DEPT

SCALE 5:1
UNITS mm

DRAWING NO. EDC3-633753-00
PART NO. CX90BW1-24P*
HRS HIROSE KOREA CO.,LTD.
CODE NO ⚠1 5 CL ****-****-*-***
1/2

HRS DRAWING FOR REFERENCE

HIROSE ELECTRIC CO., LTD. All Rights Reserved.
Aug.1.2026 Copyright 2026 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

DRAWING FOR PACKING

DIRECTION OF UNREELING



B-B



[NOTE]

1. Co-planarity of contact leads.
   - 0.08max.before reflow, 0.10max.after reflow 2times and during reflow.
2. Lot marking : 5 digits (YMDDL)



[Chart-1] LOT MARKING

Year		Month		Day		Production Line	
Ex.	Mark	Ex.	Mark	Ex.	Mark	Ex.	MARK
2020	0	Jan.	1	1st	01	Sample	S
2021	1	Feb.	2	2nd	02	MP Manual#1	1
2022	2	Mar.	3	3th	03	MP Manual#2	2
2023	3	Apr.	4	4th	04	MP Manual#3	3
2024	4	May	5	5th	05	MP Manual#4	4
2025	5	Jun.	6	6th	06	···	···
2026	6	Jul.	7	7th	07	MP Auto#1	A
2027	7	Aug.	8	8th	08	MP Auto#2	B
2028	8	Sep.	9	9th	09	MP Auto#3	C
2029	9	Oct.	A	10th	10	MP Auto#4	D
		Nov.	B	11th	11	MP Auto#5	E
		Dec.	C	···	···	···	···

3. Carrier tape packing

   Packing quantity : 1,400EA/REEL

   Cover tape peeling force : 10~130gf(0.1~1.3N) @ 300mm/min



4. Pickup area

5. Series P/N Marking

No.	P/N	Marking	Code No.	Description
1	CX90BW1-24P	CX90BW1-24P	CL 6247-0001-3-000	IP54, Air leak Full-inspection
2	CX90BW1-24P1	CX90BW1-24P1	CL 6247-0003-9-000	IP68, Air leak Full-inspection

PIN ASSIGNMENT(FRONT-VIEW)



A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-	Vbus	CC1	D+	D-	SBU1	Vbus	RX2-	RX2+	GND
GND	RX1+	RX1-	Vbus	SBU2	D-	D+	CC2	Vbus	TX2-	TX2+	GND
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1

C-C



HRS DRAWING FOR REFERENCE



NO.	DESCRIPTIONS	MATERIAL	FINISH	REMARKS
10	REEL BOBBIN	PS	-	
9	COVER TAPE	PET	-	
8	EMBOSS TAPE	PS	Thermo-Comperssion Sealing	

SCALE 4:1
UNITS mm

DRAWING NO. EDC3-633753-00

PART NO. CX90BW1-24P*

HRS HIROSE KOREA CO.,LTD.

CODE NO 3 5 CL ****-****-*-***

2/2