


Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



CROSS CUT SECTION (10:1)



RECOMMENDED LAND PATTERN DIMENSION OF PCB
(RECOMMENDED METAL MASK THICKNESS:0.15mm)



HRS DRAWING FOR REFERENCE

NOTES
1. SMT LEAD-COPLANARITY:0.1 MAX.
2. THIS PRODUCT HAS NO POLARITY TO PATTERN FOR MOUNTING.
3. THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.
4. STACKING HEIGHT FROM LEAD TO LEAD(REFERENCE DIMENSIONS)
5. BOARD DISTANCE
6. AREA IS VACUUM PICKUP AREA FOR REFERENCE.

NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
3	COPPER ARROY	CONTACT AREA:GOLD 0.76μm min. LEAD AREA:GOLD 0.03μm min. UNDER PLATING:NICKEL 1.3μm min.	6	PET	TOP COVER TAPE
			5	PS	EMBOSSED CARRIER TAPE
			4	COPPER ARROY	SURFACE AREA:GOLD 0.03μm min. UNDER PLATING:NICKEL 1.3μm min.
1, 2	LCP	BEIGE UL94V-0			


UNITS	SCALE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	4 : 1					

HIROSE ELECTRIC CO., LTD.

APPROVED	HS. OKAWA	11. 03. 24	DRAWING NO. EDC3-330881-01
CHECKED	KI. HIROKAWA	11. 03. 24	PART NO. FX10A-168P-SV3(83)
DESIGNED	DK. AIMOTO	11. 03. 23	CODE NO. CL570-0304-7-83
DRAWN	DK. AIMOTO	11. 03. 23	△ 1/2

Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


DRAWING FOR PACKING(2:1)



A(5:1)



REELED DIMENSION(FREE)



HRS DRAWING FOR REFERENCE

NOTES 1 1REEL:800 CONNECTORS.
2 MINIMUM 10 COMPARTMENTS FROM BOTH REEL ENDS REMAIN EMPTY.
3 THIS PRODUCT HAS NO POLARITY TO TAPE AND REEL PACKAGING.
4 THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

HRS	DRAWING NO.	EDC3-330881-01
	PART NO.	FX10A-168P-SV3(83)
	CODE NO.	CL570-0304-7-83 △ 2/2