


Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




CODE No.	PART No.	NUMBER OF CONTACT	A	B	C
CL543-0682-1-57	DF11C- 4DP-2V(57)	4	2	8.5	8.7
CL543-0683-4-57	DF11C- 6DP-2V(57)	6	4	10.5	10.7
CL543-0684-7-57	DF11C- 8DP-2V(57)	8	6	12.5	12.7
CL543-0685-0-57	DF11C-10DP-2V(57)	10	8	14.5	14.7
CL543-0686-2-57	DF11C-12DP-2V(57)	12	10	16.5	16.7
CL543-0687-5-57	DF11C-14DP-2V(57)	14	12	18.5	18.7
CL543-0688-8-57	DF11C-16DP-2V(57)	16	14	20.5	20.7
CL543-0689-0-57	DF11C-18DP-2V(57)	18	16	22.5	22.7
CL543-0690-0-57	DF11C-20DP-2V(57)	20	18	24.5	24.7
CL543-0691-2-57	DF11C-22DP-2V(57)	22	20	26.5	26.7
CL543-0692-5-57	DF11C-24DP-2V(57)	24	22	28.5	28.7
CL543-0693-8-57	DF11C-26DP-2V(57)	26	24	30.5	30.7
CL543-0694-0-57	DF11C-28DP-2V(57)	28	26	32.5	32.7
CL543-0695-3-57	DF11C-30DP-2V(57)	30	28	34.5	34.7
CL543-0696-6-57	DF11C-32DP-2V(57)	32	30	36.5	36.7
CL543-0697-9-57	DF11C-40DP-2V(57)	40	38	44.5	44.7





3 RECOMMENDED PATTERN(2:1)



NOTES 1: IF THERE IS PATTERN ON ▨ PART, THERE IS A POSSIBILITY THAT IT WILL MAKE CONTACT WITH THE LEADS.
2 : LEAD CO-PLANARITY INCLUDE REINFORCED METAL FITTINGS SHALL BE 0.1mm MAX.
3: RECOMMENDED METAL MASK THICKNESS:0.15-0.2mm
OPEN AREA RETIO:100%

NO.	MATERIAL	FINISH , REMARKS
2	POLYAMIDE	BEIGE. UL94V-0
1	BRASS	SURFACE:GOLD PLATED 0.2μm min UNDER PLATING:NICKEL PLATED 1μm min

NO.	MATERIAL	FINISH , REMARKS
7	PS	REEL
6	POLYESTER	CLEAR(COVER TAPE)
5	PS	CLEAR(EMBOSSED CARRIER TAPE)
4	POLYAMIDE	CAP, BLACK
3	BRASS	TIN PLATED 1μm min


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	5 : 1	2	1	DIS-H-00011128	TS. MIYAKI	SZ. ONO	20211006


HIROSE ELECTRIC CO., LTD.	APPROVED : TS. SAKATA	20080401	DRAWING NO. EDC-163554-57-04
	CHECED : TS. KUMAZAWA	20080401	PART NO. DF11C-*DP-2V(57)
	DESIGNED : KT. ISHII	20080401	CODE NO. CL543- 2 1/2
	DRAWN : YK. NAKATSU	20080313	

HRS DRAWING FOR REFERENCE

Feb.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


HRS DRAWING FOR REFERENCE







CODE No.	NUMBER OF CONTACT	D	E	F	G	H
DF11C- 4DP-2V(57)	4	24.0	—	11.5	13.2	24.4
DF11C- 6DP-2V(57)	6	24.0	—	11.5	15.2	24.4
DF11C- 8DP-2V(57)	8	24.0	—	11.5	17.2	24.4
DF11C-10DP-2V(57)	10	32.0	28.4	14.2	19.2	32.4
DF11C-12DP-2V(57)	12	32.0	28.4	14.2	21.2	32.4
DF11C-14DP-2V(57)	14	44.0	40.4	20.2	23.2	44.4
DF11C-16DP-2V(57)	16	44.0	40.4	20.2	25.2	44.4
DF11C-18DP-2V(57)	18	44.0	40.4	20.2	27.2	44.4
DF11C-20DP-2V(57)	20	44.0	40.4	20.2	29.2	44.4
DF11C-22DP-2V(57)	22	44.0	40.4	20.2	31.2	44.4
DF11C-24DP-2V(57)	24	56.0	52.4	26.2	33.2	56.4
DF11C-26DP-2V(57)	26	56.0	52.4	26.2	35.2	56.4
DF11C-28DP-2V(57)	28	56.0	52.4	26.2	37.2	56.4
DF11C-30DP-2V(57)	30	56.0	52.4	26.2	39.2	56.4
DF11C-32DP-2V(57)	32	56.0	52.4	26.2	41.2	56.4
DF11C-40DP-2V(57)	40	72.0	68.4	34.2	49.2	72.4


STYLE AND DIMENSION OF REEL







DETAIL OF NOTE LABEL



NOTES 4 :1 REEL:500 CONNECTORS.

5 :AT THE BIGINNING OF THE REEL, 15 COMPONENTS SHALL BE EMPTY. AT THE END OF THE REEL, 10 COMPONENTS SHALL BE EMPTY.

6 :WHEN THE TAPE WIDTH IS 32, 44, 56 OR 72mm, SPROCKET HOLES SHALL BE SET ON BOTH SIDES OF REEL AS SHOWN ON THIS DRAWING.

7 :THE REEL IS WRAPPED IN ALUMINIUM BAG WITH A DRY AGENT INSIDE FOR MOISTURE-PROOF PACKAGING.

8 :FOR THE STORAGE OF 168 HOURS OR MORE AFTER OPENING THE PACKAGE, KEEP THE PRODUCTS UNDER MOISTURE PROOF CONDITIONS.

9 :EXCEPT ON THE MATING SURFACE, COMPONENT INFLATION DOES NOT AFFECT THE PRODUCTS PERFORMANCE.

DRAWING NO.	EDC-163554-57-04
PART NO.	DF11C-*DP-2V(57)
CODE NO.	CL543-

△2 2/2