








- NOTES
- 1 PLATING(REF.NO. ③,④)
CONTACT AREA : GOLD 0.2μm min
OTHERS : GOLD AND NICKEL
UNDER PLATING : NICKEL 2μm min
 - 2 THE RECOMMENDED CLAMP TORQUE OF REF.NO.⑧ TO BE 1.5 TO 2N·m.
THREAD LOCKER TO THE THREADED PORTION OF REF.NO.④ IS RECOMMENDED TO PREVENT REF.NO.⑧ FROM LOOSING.
RECOMMENDED THREAD LOCKER:LOCTITE 271, HENKEL JAPAN LTD.
 - 3 WHEN THIS CONNECTOR IS MOUNTED ON TO PANEL, BE CAREFUL REF.NO.⑥ IS ASSEMBLED SURELY INTO THE GROOVE OF REF.NO.⑥ AS SHOWN IN THIS FIGURE TO KEEP WATERPROOF EFFECTIVENESS.

| | | | | | |
|-----|-----------------|---|-----|--------------------|------------------|
| 4 | SHOSPHOR BRONZE |  | 8 | BRASS | NICKEL PLATING |
| 3 | SHOSPHOR BRONZE |  | 7 | SHOSPHOR BRONZE | NICKEL PLATING |
| 2 | PPS | (BLACK) UL94V-0 | 6 | CHLOROPRENE RUBBER | (BLACK) |
| 1 | ZINC ALLOY | NICKEL PLATING | 5 | SHOSPHOR BRONZE | NICKEL PLATING |
| NO. | MATERIAL | FINISH . REMARKS | NO. | MATERIAL | FINISH . REMARKS |

| | | | | | | | |
|---|---|------------------------|---|---|------------|-----------|------------|
| UNITS mm |  | SCALE 4 : 1 | COUNT | DESCRIPTION OF REVISIONS | DESIGNED | CHECKED | DATE |
| | | |  1 | DIS-C-002180 | HK. NAMA I | HY. KISHI | 11. 05. 13 |
|  HIROSE ELECTRIC CO., LTD. | | APPROVED : MR. YOSHIDA | 05. 01. 05 | DRAWING NO. EDC3-114247-00 | | | |
| | | CHECKED : MO. SATOH | 05. 01. 05 | PART NO. LF10WBR-12S | | | |
| | | DESIGNED : YH. YAMADA | 05. 01. 05 | CODE NO. CL136-1008-6-00 | | | |
| | | DRAWN : YH. YAMADA | 05. 01. 05 |   | | | |