



May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




ELV. RoHS COMPLIANT



MATED CONNECTORS (FREE)




RECOMMENDED PCB PATTERN (FREE)
OPEN AREA RATIO : 100%



NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM

NO. OF CYCLES : 1R IN THE AIR OR NITROGEN
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C
90~120s

2. TEMPERATURE FOR SOLDERING IRON : 350~380°C WITHIN 5s
3. CO-PLANARITY : 0.1mm MAX
4. RECOMMENDED SOLDER THICKNESS : 0.10mm




3	BRASS	TIN PLATING	6	POLYSTYRENE	
2	BRASS	Au PLATING	5	POLYESTER	
1	LCP	BLACK	4	POLYSTYRENE	
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 5:1	COUNT 3	DESCRIPTION OF REVISIONS DIS-T-00020330	DESIGNED RS. TAKAGI
		APPROVED : HK. UMEHARA	2020. 12. 24	DRAWING NO. EDC-392585-00-00	
		CHECKED : OM. MIYAMOTO	2020. 12. 24	PART NO. GT50-2P-1H	
		DESIGNED : YT. TAKANASHI	2020. 12. 22	CODE NO. CL0760-1002-0-00	
		DRAWN : YT. TAKANASHI	2020. 12. 22		
				DATE 2024. 03. 05	


May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

PACKING STYLE (FREE)

REEL DIMENSION




PACKING STYLE DRAWING




※Embossed pocket has a different shape to prevent overlapping, and the drawing shows a representative shape.

PRODUCTS DIRECTION



CARDBOARD DIMENSION

W = (405) (mm)
D = (405) (mm)
H = (31) (mm)



HRS	DRAWING NO.	EDC-392585-00-00	
	PART NO.	GT50-2P-1H	
	CODE NO.	CL0760-1002-0-00	
		3	2/2