

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV, RoHS COMPLIANT





PIN ASSIGNMENT
8 7 6 5 4 3 2 1
16 15 14 13 12 11 10 9



RECOMMENDED PCB PATTERN








HRS DRAWING FOR REFERENCE

NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM
: IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250℃
OVER 230℃ : 20~40s
PREHEAET : 150~180℃
60~120s
2. TEMPERATURE FOR SOLDERING IRON
:280~300℃ WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
3	BRASS	TIN PLATED T=0.64	6	PET	
2	BRASS	TIN PLATED T=0.64	5	PS	
1	PPS	BLACK	4	BRASS	TIN PLATED T=0.4

UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	△0					

HIROSE ELECTRIC CO., LTD.


APPROVED	NH. NAKATA	16. 03. 28
CHECKED	HS. OZAWA	16. 03. 27
DESIGNED	TK. SHISHIKURA	16. 03. 26
DRAWN	TK. SHISHIKURA	16. 03. 26

DRAWING NO.	EDC-361741-00-00
PART NO.	GT25H2-16DP-2. 2H
CODE NO.	CL775-0089-4-00


△0 1/2

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

PACKAGING SPECIFICATION




REEL DIMENSION(FREE)



(200PCS/REEL)
PACKAGING SPECIFICATION OF EMBOSS CARRIER TAPE

CARDBOARD DIMENSION(FREE)



BOX SIZE
W=(405)(mm)
D=(405)(mm)
H=(49) (mm)

1REEL/BOX

HRS DRAWING FOR REFERENCE

HRS	DRAWING NO.	EDC-361741-00-00
	PART NO.	GT25H2-16DP-2.2H
	CODE NO.	CL775-0089-4-00

△0 2/2