

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


ELV. RoHS COMPLIANT





PIN ASSIGNMENT
10 20 9 19 8 18 7 17 6 16 5 15 4 14 3 13 2 12 1 11



RECOMMENDED PCB PATTERN








HRS DRAWING FOR REFERENCE

NOTE1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM
: IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250℃
OVER 230℃ : 20~40s
PREHEAT : 150~180℃
60~120s
2. TEMPERATURE FOR SOLDERING IRON
:280~300℃ WITHIN 2s
3. LEAD CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
3	BRASS	TIN PLATED	6	PET	
2	BRASS	TIN PLATED	5	PS	
1	PA	BLACK	4	BRASS	TIN PLATED


UNITS	SCALE		COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
mm	2 : 1	△2	1	DIS-T-00006626	DONGCHAN KIM	HH. TSUKUMO	20200902

HIROSE ELECTRIC CO., LTD.


APPROVED	AR. SHIRAI	20180622	DRAWING NO. EDC-358751-10-00
CHECKED	HS. OZAWA	20180622	PART NO. GT25H2-20DP-2.2H(10)
DESIGNED	YT. HAYAKAWA	20180622	
DRAWN	GYEONGMIN LEE	20180622	CODE NO. CL775-0080-0-10 △2 1/2

Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


PACKAGING SPECIFICATION



⚠2 REEL DIMENSION (FREE)



CARDBOARD DIMENSION (FREE)



BOX SIZE
W=(405)(mm)
D=(405)(mm)
H=(63) (mm)

1 REEL / BOX

HRS DRAWING FOR REFERENCE

HRS	DRAWING NO.	EDC-358751-10-00
	PART NO.	GT25H2-20DP-2.2H(10)
	CODE NO.	CL775-0080-0-10 ⚠2 2/2