



1	2	3	4										
													
<table border="1"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~04*1TV~</td><td>WHITE</td></tr><tr><td>~04*2TV~</td><td>BLACK</td></tr></tbody></table>				Part No.	Cable color	~04*1TV~	WHITE	~04*2TV~	BLACK				
Part No.	Cable color												
~04*1TV~	WHITE												
~04*2TV~	BLACK												
NOTE ① We indicate the length of the harness on the last of product name, 'L' part. ② Tolerance for [L] <table border="1"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>$35 \leq L \leq 200$</td><td>± 4</td></tr><tr><td>$200 < L \leq 500$</td><td>± 8</td></tr><tr><td>$500 < L \leq 1000$</td><td>± 12</td></tr><tr><td>$1000 < L$</td><td>$\pm 1.5\%$</td></tr></tbody></table> ③ Connector rotation angle is within ± 45 degree from the above image. For long length in the case of $L > 500$, the angle is optional. 4. Specifications are subject to change without notice. 【 DIMENSIONS OF CONNECTOR 】 				Length L [mm]	Tolerance [mm]	$35 \leq L \leq 200$	± 4	$200 < L \leq 500$	± 8	$500 < L \leq 1000$	± 12	$1000 < L$	$\pm 1.5\%$
Length L [mm]	Tolerance [mm]												
$35 \leq L \leq 200$	± 4												
$200 < L \leq 500$	± 8												
$500 < L \leq 1000$	± 12												
$1000 < L$	$\pm 1.5\%$												
1	U.FL-LP-040HF	CL331-0557-3	2	0.81 Dia. coaxial cable	HALOGEN FREE								
NO.	PART NO.	CODE NO.	NO.	PART NO.									
UNITS mm		SCALE FREE	COUNT ① 1	DESCRIPTION OF REVISIONS DIS-D-00003245	DESIGNED MS. MATSUMOTO	CHECKED MT. KANEKO	DATE 18. 06. 15						
 HIROSE ELECTRIC CO., LTD.		APPROVED : KH. IKEDA	18. 02. 15	DRAWING NO.									
		CHECKED : TS. NOBE	18. 02. 15	PART NO. UFL-2LPHF6-04**TV-AC-L ① ①									
		DESIGNED : MS. MATSUMOTO	18. 02. 15	CODE NO.									
		DRAWN : MS. MATSUMOTO	18. 02. 15	① ①									
FORM HC0011-5-51		2	3	4									