

1		2		3		4							
				<table border="1"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~044*1TS~</td><td>WHITE</td></tr><tr><td>~044*2TS~</td><td>BLACK</td></tr></tbody></table>				Part No.	Cable color	~044*1TS~	WHITE	~044*2TS~	BLACK
Part No.	Cable color												
~044*1TS~	WHITE												
~044*2TS~	BLACK												
NOTE 1 We indicate the length of the harness on the last of product name, 'L' part. 2 The angle is optional for long length in the case of L>150. 3 Tolerance for [L]				Cable direction of recommended. For maintain performance.									
<table border="1"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>35 ≤ L ≤ 170</td><td>± 0.5 mm</td></tr></tbody></table>				Length L [mm]	Tolerance [mm]	35 ≤ L ≤ 170	± 0.5 mm						
Length L [mm]	Tolerance [mm]												
35 ≤ L ≤ 170	± 0.5 mm												
4 The drawing shows mated connector height. 5. Specifications are subject to change without notice.													
[DIMENSIONS OF CONNECTOR]				[MATED CONDITION]									
[PRECAUTIONS FOR HANDLING] - Connector insertion and extraction. a. Insert the connector as perpendicularly to the mating surface as possible with aligning the mating axes of both connectors by specialised insertion JIG. (fig.1) Part No. X.FL(V)-LP-IN.OUT (CL0331-0076-0) Do not excessively slant the connectors when inserting. b. Connector shall be extracted by specialised extraction JIG. (fig.2) Part No. X.FL(V)-LP-IN.OUT (CL0331-0076-0) Never hold the cable when extracting the cable because it damages the connector. - Allowable loads on the cable after the connectors are mated. Fig.3 show the maximum allowable loads on the cable. Do not apply loads exceeding these values to the cable. - We recommended you to arrange a cushioning medium, as shown in fig.4 and to prevent a fitting blank.													
1		X.FL(V)-LP(P)-044		CL331-2300-0		2							
No.		Part No.		Code No.		No.							
						0.64 Dia. coaxial cable							
						Part No.							
UNITS mm				SCALE FREE		COUNT							
						DESCRIPTION OF REVISIONS							
						DESIGNED							
						CHECKED							
						DATE							
F				HIROSE ELECTRIC CO., LTD.		APPROVED : NK. NINOMIYA 20230608							
						DRAWING NO.							
						PART NO.							
						CODE NO.							
						XFL-2LPV-044**TS-A-L 1							
						1/1							

FORM HC0011-5-51