

Part No.	Cable color
~084N1~	White
~084N2~	Black
~084N4~	Blue

NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.


2 Tolerance for [L]

Length L [mm]	Tolerance [mm]
$35 \leq L \leq 200$	$\pm 4$
$200 < L \leq 500$	$\pm 8$
$500 < L \leq 1000$	$\pm 12$
$1000 < L$	$\pm 1.5\%$

3 Connector rotation angle is within  $\pm 45$  degree from the above image.  
For long length in the case of  $L > 500$ , the angle is optional.

4. Specifications are subject to change without notice.


#### [ DIMENSIONS OF CONNECTOR ]



For stable supply of this series,  
material supplier of piece part#1  
will be changed during 2019-2022.  
Please note this change in advance.  
There will be no difference in product  
performance and quality. 1

#### [ PRECAUTIONS FOR HANDLING ]

- ◆ Connector insertion and extraction
  - a. Connector shall be extracted vertically by specialised extraction JIG.  
Part No.: H.FL-LP-NCCL Code: CL331-0551-7)  
Never hold the cable when extracting the cable because it damages the connector.
  - b. Insert the connector as perpendicularly to the mating surface as possible by aligning the mating axes of both connectors. Do not excessively slant the connectors when inserting.



1	H.FL75-LP(G)-084	CL331-0808-1	2	1.5Dia. coaxial cable			
NO.	PART NO.	CODE NO.	NO.	PART NO.			
UNITS mm		SCALE FREE	COUNT 1	DESCRIPTION OF REVISIONS DIS-D-00003769	DESIGNED MS. MATSUMOTO	CHECKED MT. KANEKO	DATE 20181218
APPROVED : NK. NINOMIYA 20161108		DRAWING NO. EDC-373598-00-00					
CHECKED : NK. NINOMIYA 20161108		PART NO. H.FL75-2LPG-084N*-A-L 1					
DESIGNED : KS. TAKAHASHI 20161108		CODE NO. CL321-5111-4-00 1/1					
DRAWN : KS. TAKAHASHI 20161108							