






May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


A
B
C
D
E
F




- NOTE
- 1. ALL LEAD CO-PLANARITY SHALL BE 0.08mm MAX.
 - 2. CONTACT PLATING SPECIFICATIONS
CONTACT AREA : GOLD 0.05 μ m MIN
SMT LEAD : GOLD 0.05 μ m MIN
UNDERPLATING : NICKEL 1 μ m MIN
(SURFACE : SEALING)
 - 3. CAV NO. ARE INDICATED IN APPROX POSITION SHOWN.

	COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	B	Y	CHKD	DATE
△						. .	△						. .
△						. .	△						. .
△						. .	△						. .

ENGAGEMENT FIGURE (50:1)




SIGNAL CONTACT




POWER CONTACT

4	PS	CLEAR (EMBOSSED CARRIER TAPE)						
3	COPPER ALLOY	2						
2	COPPER ALLOY	2	6	PS	BLACK (PLASTIC REEL)			
1	LCP	UL94 V-0, BLACK	5	POLYESTER	CLEAR (COVER TAPE)			
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS			
REMARKS				DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
				J. M. YEOM 20. 09. 09	J. M. YEOM 20. 09. 09	H. W. JO 20. 09. 09	H. W. JO 20. 09. 09	22. 06. 07
CODE NO. (OLD)		DRAWING NO. EDC3-633199-80		PART NO. BK13C06-16DS/2-0.35V(800)				
	SCALE 10:1							
	UNITS mm	 HIROSE KOREA CO., LTD.		CODE NO CL 6665-0042-5-800			1 3	


5



METAL MASK THICKNESS : $80\text{ }\mu\text{m}$



4



```

REFLOW METHOD : N2 REFLOW
NUMBER OF REFLOW CYCLES : 2 CYCLES MAX.
1) REFLOW TIME
  DURATION ABOVE 220℃, 60 SEC MAX.
  (PEAK TEMPERATURE : 250℃ MAX)
2) PRE-HEAT TIME
  PRE-HEAT TEMPERATURE(MIN): 150℃
  PRE-HEAT TEMPERATURE(MAX): 180℃
  PRE-HEAT TIME: 90-120 SEC.

```


4

5


	DRAWING NO. EDC3-633199-80		PART NO. BK13C06-16DS/2-0.35V(800)	
	SCALE 10:1 UNITS mm		CODE NO CL 6665-0042-5-800	
 HIROSE KOREA CO., LTD.			2	

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


EMBOSSED CARRIER TAPE PACKAGING (5:1)





D-D (5:1)



C-C (5:1)




DIRECTION OF UNREELING



TAPING(FREE)

STYLE AND DIMENSION OF REEL (FREE)



DETAIL OF PART No. LABEL

SUPPLIER	
QUANTITY	
PART NO.	
CODE NO.	
DATE OF MANUFACTURED	
生産月日	年 月 日
図番	** ** *
品名	BK13C06-16DS/2-0.35V(800)
納入数量	20,000個
納入者	HIROSE KOREA

8 . PER REEL 20,000 CONNECTORS.

9 . THE DIMENSIONS IN PARENTHESES ARE FOR REFERENCE.

10 > REFER TO JIS C 0806, IEC-60286-3 (PACKAGING OF COMPONENTS FOR AUTOMATIC HANDLING)

DRAWING NO.	EDC3-633199-80	PART NO.	BK13C06-16DS/2-0.35V(800)
SCALE	10:1	CODE NO.	CL 6665-0042-5-800
UNITS	mm		

HIROSE KOREA CO., LTD.

3/3