







1	2	3	4																																	
A				A																																
B	<table border="1" data-bbox="1037 649 1348 779"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~062*1D~</td><td>GRAY</td></tr><tr><td>~062*2D~</td><td>BLACK</td></tr></tbody></table>			Part No.	Cable color	~062*1D~	GRAY	~062*2D~	BLACK	B																										
Part No.	Cable color																																			
~062*1D~	GRAY																																			
~062*2D~	BLACK																																			
C	<p>NOTE 1 We indicate the length of the harness on the last of product name, 'L' part.</p> <p>2 Tolerance for [ L ]</p> <table border="1" data-bbox="454 1041 1066 1249"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td><math>35 \leq L \leq 200</math></td><td><math>\pm 4</math></td></tr><tr><td><math>200 &lt; L \leq 500</math></td><td><math>\pm 8</math></td></tr><tr><td><math>500 &lt; L \leq 1000</math></td><td><math>\pm 12</math></td></tr><tr><td><math>1000 &lt; L</math></td><td><math>\pm 1.5\%</math></td></tr></tbody></table>			Length L [mm]	Tolerance [mm]	$35 \leq L \leq 200$	$\pm 4$	$200 < L \leq 500$	$\pm 8$	$500 < L \leq 1000$	$\pm 12$	$1000 < L$	$\pm 1.5\%$	C																						
Length L [mm]	Tolerance [mm]																																			
$35 \leq L \leq 200$	$\pm 4$																																			
$200 < L \leq 500$	$\pm 8$																																			
$500 < L \leq 1000$	$\pm 12$																																			
$1000 < L$	$\pm 1.5\%$																																			
D	<p>3 Connector rotation angle is within <math>\pm 45</math> degree from the above image. For long length in the case of <math>L &gt; 500</math>, the angle is optional.</p> <p>4. Specifications are subject to change without notice.</p> <p>【 DIMENSIONS OF CONNECTOR 】</p> 			D																																
E	<table border="1" data-bbox="183 1877 1141 1953"><thead><tr><th>1</th><th>U. FL-LP-062HF(06)</th><th>CL331-0561-0-06</th><th>2</th><th>0.95 Dia. coaxial cable</th></tr></thead><tbody><tr><td>NO.</td><td>PART NO.</td><td>CODE NO.</td><td>NO.</td><td>PART NO.</td></tr></tbody></table> <div data-bbox="1252 1881 1417 1930">HALOGEN FREE</div>			1	U. FL-LP-062HF(06)	CL331-0561-0-06	2	0.95 Dia. coaxial cable	NO.	PART NO.	CODE NO.	NO.	PART NO.	E																						
1	U. FL-LP-062HF(06)	CL331-0561-0-06	2	0.95 Dia. coaxial cable																																
NO.	PART NO.	CODE NO.	NO.	PART NO.																																
F	<table border="1" data-bbox="183 1953 1513 2154"><thead><tr><th>UNITS mm</th><th>SCALE FREE</th><th>COUNT</th><th>DESCRIPTION OF REVISIONS</th><th>DESIGNED</th><th>CHECKED</th><th>DATE</th></tr></thead><tbody><tr><td rowspan="4"> HIROSE ELECTRIC CO., LTD.</td><td>APPROVED</td><td>·NK. NINOMIYA</td><td>18.06.22</td><td colspan="3">DRAWING NO.</td></tr><tr><td>CHECKED</td><td>·MT. KANEKO</td><td>18.06.22</td><td colspan="3">PART NO.</td></tr><tr><td>DESIGNED</td><td>·MS. MATSUMOTO</td><td>18.06.22</td><td colspan="3">CODE NO.</td></tr><tr><td>DRAWN</td><td>·MS. MATSUMOTO</td><td>18.06.22</td><td colspan="3">UFL-2LPHF6-062**D-A-L 1</td></tr></tbody></table> <div data-bbox="1412 2116 1508 2154"> 1/1</div>			UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	 HIROSE ELECTRIC CO., LTD.	APPROVED	·NK. NINOMIYA	18.06.22	DRAWING NO.			CHECKED	·MT. KANEKO	18.06.22	PART NO.			DESIGNED	·MS. MATSUMOTO	18.06.22	CODE NO.			DRAWN	·MS. MATSUMOTO	18.06.22	UFL-2LPHF6-062**D-A-L 1			F
UNITS mm	SCALE FREE	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE																														
 HIROSE ELECTRIC CO., LTD.	APPROVED	·NK. NINOMIYA	18.06.22	DRAWING NO.																																
	CHECKED	·MT. KANEKO	18.06.22	PART NO.																																
	DESIGNED	·MS. MATSUMOTO	18.06.22	CODE NO.																																
	DRAWN	·MS. MATSUMOTO	18.06.22	UFL-2LPHF6-062**D-A-L 1																																

FORM HC0011-5-51