





- Notes 1 This product is apply to the wire #16 to #20.
(Jacket diameter : $\phi 1.9$ to 3.2mm)
2 Applicable crimping tool : HT802/HR41A-11-16 (CL150-0408-5)(Applicable to AWG#16)
HT802/HR41A-11-18 (CL150-0404-4)(Applicable to AWG#18)
HT802/HR41A-11-20 (CL150-0407-2)(Applicable to AWG#20)
3 Applicable extraction tool : HR41A-TP(CL150-0405-7)
4 Per reel : 100 contacts
5 Contact plating : Gold plating $0.2\mu\text{m}$ min.
Terminal plating : Tin plating $0.5\mu\text{m}$ min.
Underplating : Nickel plating $2\mu\text{m}$ min.



1	Copper alloy	5						
NO.	MATERIAL	FINISH . REMARKS		NO.	MATERIAL	FINISH . REMARKS		
UNITS mm		SCALE 10 : 1	COUNT  1	DESCRIPTION OF REVISIONS DIS-C-00000101		DESIGNED HN. TANAKA	CHECKED HY. KISHI	DATE 15. 02. 10
 HIROSE ELECTRIC CO., LTD.		APPROVED +EJ. KUNII		15. 01. 22	DRAWING NO. EDC-118389-01-00			
		CHECKED +HY. KISHI		15. 01. 22	PART NO. HR41A-PC-111(C01)			
		DESIGNED +HN. TANAKA		15. 01. 22	CODE NO. CL141-0214-8-01			
		DRAWN +HN. TANAKA		15. 01. 22	 1 /  1			