




Safety standard			UL		CSA		TÜV	
Operating temperature range			-10~+60℃					
Rated voltage	Contact No. 1, 8, 9, 16		AC120V	AC250V	AC125V	AC250V	AC250V, DC300V	
	Other contacts						AC125V, DC150V	
Rated current	AWG #14		10A	3A	10A	3A	10A	
	AWG #16				8A			
	AWG #18		3A	1A	3A	1A	5A	
	AWG #20						2.5A	
	AWG #22							
	AWG #24	Contact No. 1, 8, 9, 16	2A	1A	2A	1A	1A	
		Other contacts	1A	0.5A	1A	0.5A		
		AWG #26						
AWG #28								

Contact name	Applicable wire
QR/P1-SC1A-※11	AWG #18~24
QR/P1-SC1B-※21	AWG #14~16
QR/P1-SC2A-※11	AWG #24~28
QR/P1-SC2B-※21	AWG #20~24

$\otimes : 2$ is a strip contact

- Notes
- ① The dimensional tolerance of each contact hole position to be ± 0.1 .
 - ② Operating temperature range, rated voltage and rated current are per Table-1.
 - ③ The floating bush can be moved 0.4mm max in all directions.
 - ④ Please use contacts in Table-2 for QR/P1.
5. Direction for use
- (1) Please do not use for the purpose of interrupting the current.
 - (2) Please use inside the enclosure or equipment.
6. The dimensions in parentheses are for reference.

HRS HIROSE
ELECTRIC
CO., LTD.