





APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-55 °C TO +85 °C ^{(1) (2)}	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C ⁽³⁾	
	OPERATING HUMIDITY RANGE	RH 90 % MAX ^{(2) (4)}	STORAGE HUMIDITY RANGE	RH 70 % MAX ^{(3) (4)}	
	VOLTAGE	300 V DC/AC	CURRENT 	70A (TEMPERATURE RISE 30°C MAX)	
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUAL AND WITH MEASURING INSTRUMENT	ACCORDING TO DRAWING	x	x
MARKING		CONFIRMED VISUALLY		x	x
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE [EIA-364-23]		10 mA	2 mΩ MAX. ⁽⁵⁾ MATED WITH IT-PM-2S-DIR IT-PD-2S-DIR	x	-
INSULATION RESISTANCE [EIA-364-21]		500 V DC	1000 MΩ MIN.	x	-
VOLTAGE PROOF [EIA-364-20]		1000 V AC FOR 1 MINUTE	NO FLASHOVER OR BREAKDOWN.	x	-
MECHANICAL CHARACTERISTICS					
INSERTION AND WITHDRAWAL FORCES [EIA-364-13]		MEASURED WITH RESPECT TO APPLICABLE CONNECTORS	INSERTION FORCE: 50 N MAX. WITHDRAWAL FORCE: 3 N MIN.	x	-
MECHANICAL OPERATION [EIA-364-09]		100 TIMES INSERTION AND EXTRACTION	① CONTACT RESISTANCE: 2 mΩ MAX. ⁽⁵⁾ ② NO DAMAGE, CRACKS, OR LOOSE PARTS	x	-
RANDOM VIBRATION [EIA-364-28]		FREQUENCY: 50 TO 2000 Hz POWER SPECTRAL DENSITY: 0.1 g ² /Hz FOR 90 MINUTES IN THREE DIRECTIONS * Spacers were used to maintain the distance between the PCB's during testing.	① NO ELECTRICAL DISCONTINUITY OF 1 μs OR MORE ② NO DAMAGE, CRACKS, OR LOOSE PARTS	x	-
SHOCK [EIA-364-27]		490 m/s ² , DURATION OF PULSE: 11 ms 18 TIMES TOTAL, 3 EACH DIRECTION, 3 AXIS * Spacers were used to maintain the distance between the PCB's during testing.		x	-
ENVIRONMENTAL CHARACTERISTICS					
THERMAL SHOCK [EIA-364-32]		TEMPERATURE: -55 → 20 ~ 35 → 85 → 20 ~ 35 °C TIME: 30 → 5 MAX → 30 → 5 MAX minutes 10 CYCLES	① CONTACT RESISTANCE: 2 mΩ MAX. ⁽⁵⁾ ② INSULATION RESISTANCE: 100 MΩ MIN. ③ NO DAMAGE, CRACKS, OR LOOSE PARTS	x	-
CYCLIC TEMPERATURE AND HUMIDITY [EIA-364-31]		@ 25 °C, 80% RH: 60 MIN DWELL TIME 30 MIN RAMP TIME @ 65 °C, 50% RH: 60 MIN DWELL TIME 24 CYCLES		x	-
DRY HEAT [EIA-364-17]		EXPOSED AT 105 °C, 120 hr	① CONTACT RESISTANCE: 2 mΩ MAX. ⁽⁵⁾ ② NO DAMAGE, CRACKS, OR LOOSE PARTS	x	-
MIXED FLOWING GAS [EIA-364-65]		EXPOSED AT 30 °C, 70% Cl ₂ : 10 ppb, NO ₂ : 200 ppb, H ₂ S: 10 ppb, SO ₂ : 100 ppb UNMATED 7 DAYS, MATED 7 DAYS	① CONTACT RESISTANCE: 2 mΩ MAX. ⁽⁵⁾	x	-
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	1	DIS-F-00020361	TH. SANO	TY. TAKADA	20240508
REMARKS (1) INCLUDE TEMPERATURE RISE CAUSED BY CURRENT-CARRYING. (2) OPERATING TEMPERATURE SHOULD BE -55 TO 55°C WHEN HUMIDITY EXCEEDS 80% RH. (3) "STORAGE" MEANS A LONG-TERM STORAGE STATE FOR THE UNUSED PRODUCT BEFORE ASSEMBLY TO PCB. (4) NO DEW CONDENSATION IS PERMITTED. (5) THE VALUE OF CONTACT RESISTANCE INCLUDES 2 CONTACT POINTS AND THE BULK RESISTANCE. (6) THIS APPLIES TO SEALED PLASTIC BAGS. OPEN BAGS MUST BE PROTECTED FROM MOISTURE, SULFUR AND CHLORIDE WHICH CAN CAUSE THE SILVER PLATING TO TARNISH. Unless otherwise specified, the test method apply for IEC-60512.			APPROVED	MK. EZAKI	20150926
			CHECKED	MK. EZAKI	20150926
			DESIGNED	NY. SHIMURA	20150926
			DRAWN	NY. SHIMURA	20150926
Note: QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-357298-11-00
	SPECIFICATION SHEET		PART NO.	IT-P-2P-37H(11)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0636-0620-4-11	 1/1