

1		2		3		4									
				<table border="1"><thead><tr><th>Part No.</th><th>Cable color</th></tr></thead><tbody><tr><td>~068Y1T~</td><td>GRAY</td></tr><tr><td>~068Y2T~</td><td>BLACK</td></tr><tr><td>~068Y3T~</td><td>WHITE</td></tr></tbody></table>		Part No.	Cable color	~068Y1T~	GRAY	~068Y2T~	BLACK	~068Y3T~	WHITE		
Part No.	Cable color														
~068Y1T~	GRAY														
~068Y2T~	BLACK														
~068Y3T~	WHITE														
NOTE 1 We indicate the length of the harness on the last of product name, 'L' part. 2 The angle is optional for long length in the case of L>250. 3 Tolerance for [L]		【 DIMENSIONS OF CONNECTOR 】													
		<table border="1"><thead><tr><th>Length L [mm]</th><th>Tolerance [mm]</th></tr></thead><tbody><tr><td>100 ≤ L ≤ 200</td><td>± 4 mm</td></tr><tr><td>200 < L ≤ 500</td><td>± 8 mm</td></tr><tr><td>500 < L ≤ 1000</td><td>± 12 mm</td></tr></tbody></table>		Length L [mm]	Tolerance [mm]	100 ≤ L ≤ 200	± 4 mm	200 < L ≤ 500	± 8 mm	500 < L ≤ 1000	± 12 mm				
Length L [mm]	Tolerance [mm]														
100 ≤ L ≤ 200	± 4 mm														
200 < L ≤ 500	± 8 mm														
500 < L ≤ 1000	± 12 mm														
		※ For L longer than 1000mm or shorter than 100mm, please contact our representatives. 4. Specifications are subject to change without notice.													
		【 PRECAUTIONS FOR HANDLING 】 1. Connector insertion and extraction (1) Insert the connector as perpendicularly to the mating surface as possible with aligning the mating axes of both connectors by specialised insertion JIG. Part No.: U.FL(A)-LP-IN.OUT<CL331-2401-0> (fig.1) ◆ Do not excessively slant the connectors when inserting. (2) Connector shall be extracted by specialised extraction JIG. Part No.: U.FL(A)-LP-IN.OUT<CL331-2401-0> (fig.2) ◆ Never hold the cable when extracting the cable because it damages the connector. 2. Allowable loads on the cable after the connectors are mated. The below figures show the maximum allowable loads on the cable. (fig.3) ◆ Do not apply loads exceeding these values to the cable.													
1 U.FL(A)-LP(P)-068		CL331-2402-0		2 1.13 Dia. coaxial cable		HALOGEN FREE									
No. Part No.		Code No.		No. Part No.											
UNITS mm		SCALE FREE		COUNT 1		DESCRIPTION OF REVISIONS									
						DIS-D-00006261									
DESIGNED MS. MATSUMOTO		CHECKED MT. KANEKO		DATE 20210122											
DRAWN MK. INOUE		APPROVED NK. NINOMIYA													
20200220		20200220													
20200220		20200220													
20200220		20200220													
DRAWING NO.		PART NO.		CODE NO.		UFL-2LPA-068Y*T-A-L 1									
1		1		1		1									

FORM HC0011-5-51