






May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



| Code No.        | Part No.        | Number of contact | A    | B    | C    |
|-----------------|-----------------|-------------------|------|------|------|
| CL543-0031-3-22 | DF3- 2P-2DS(22) | 2                 | 6.0  | 4.6  | 2.0  |
| CL543-0032-6-22 | DF3- 3P-2DS(22) | 3                 | 8.0  | 6.6  | 4.0  |
| —               | DF3- 4P-2DS(22) | 4                 | 10.0 | 8.6  | 6.0  |
| —               | DF3- 5P-2DS(22) | 5                 | 12.0 | 10.6 | 8.0  |
| —               | DF3- 6P-2DS(22) | 6                 | 14.0 | 12.6 | 10.0 |
| —               | DF3- 7P-2DS(22) | 7                 | 16.0 | 14.6 | 12.0 |
| —               | DF3- 8P-2DS(22) | 8                 | 18.0 | 16.6 | 14.0 |
| —               | DF3- 9P-2DS(22) | 9                 | 20.0 | 18.6 | 16.0 |
| —               | DF3-10P-2DS(22) | 10                | 22.0 | 20.6 | 18.0 |
| —               | DF3-11P-2DS(22) | 11                | 24.0 | 22.6 | 20.0 |
| —               | DF3-12P-2DS(22) | 12                | 26.0 | 24.6 | 22.0 |
| —               | DF3-13P-2DS(22) | 13                | 28.0 | 26.6 | 24.0 |
| —               | DF3-14P-2DS(22) | 14                | 30.0 | 28.6 | 26.0 |
| —               | DF3-15P-2DS(22) | 15                | 32.0 | 30.6 | 28.0 |



Note 1: No.1 and \* Contact shall be processed kink. (\*=2-15)

|             |           |                                                 |            |                          |                                                                          |
|-------------|-----------|-------------------------------------------------|------------|--------------------------|--------------------------------------------------------------------------|
| 1           | Polyamide | Black, UL94V-0<br>(Fiberglass reinforced resin) | 2          | Brass                    | Surface:Gold plated 0.2μm min.<br>Under plating:Nickel plated 0.5μm min. |
| NO.         | MATERIAL  | FINISH . REMARKS                                | NO.        | MATERIAL                 | FINISH . REMARKS                                                         |
| UNITS<br>mm |           | SCALE<br>5 : 1                                  | COUNT<br>  | DESCRIPTION OF REVISIONS | DESIGNED                                                                 |
|             |           | APPROVED : HS. OKAWA                            | 17. 02. 28 | DRAWING NO.              | EDC-162397-22-00                                                         |
|             |           | CHECKED : TS. FUKUSHIMA                         | 17. 02. 28 | PART NO.                 | DF3- * P-2DS(22)                                                         |
|             |           | DESIGNED : TO. KUROMATSU                        | 17. 02. 28 | CODE NO.                 | CL543-                                                                   |
|             |           | DRAWN : MI. SAKIMURA                            | 17. 02. 28 |                          |                                                                          |