



APPLICABLE STANDARD					
RATING	Operating temperature range	-40 °C to 125 °C	Storage temperature range	-10 °C to 50 °C (Packed condition)	
	Voltage	40 V AC / DC	Operating or storage humidity range	Relative humidity 90% MAX (Not dewed)	
	Current	0.4 A	Applicable cable	t = 0.3 ± 0.05 mm, Gold plating Heat resistance : 125 °C	
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
General examination	Visually and by measuring instrument.		According to drawing.	×	×
Marking	Confirmed visually.			×	×
ELECTRICAL CHARACTERISTICS					
Contact resistance	1 mA (DC or 1000 Hz).		50 mΩ MAX. Including FPC bulk resistance (L = 8 mm)	×	—
Insulation resistance	100 V DC.		500 MΩ MIN.	×	—
Voltage proof	150 V AC for 1 min.		No breakdown.	×	—
MECHANICAL CHARACTERISTICS					
Mechanical operation	20 times insertions and extractions.		① Contact resistance : 50 mΩ MAX. ② No damage, crack and looseness of parts. ① No electrical discontinuity of 1 μs. ② Contact resistance : 50 mΩ MAX. ③ No damage, crack and looseness of parts.	×	—
Vibration	Frequency 10 to 55 Hz, half amplitude 0.75 mm, for 10 cycles in 3 axial directions.			×	—
Shock	981 m/s ² , duration of pulse 6 ms at 3 times in 3 both axial directions.			×	—
FPC retention force	Measured by applicable FPC. (Connector, FPC at initial condition. Thickness of FPC shall be t = 0.30 mm)		Direction of insertion : 0.4 × n N MIN. (n : Number of contacts) (note 1)	×	—
ENVIRONMENTAL CHARACTERISTICS					
Rapid change of temperature	Temperature -55→+15 to +35→+125→+15 to +35 °C Time 30→ 2 to 3 → 30 → 2 to 3 min. Under 1000 cycles.		① Contact resistance : 50 mΩ MAX. ② Insulation resistance : 50 MΩ MIN. ③ No damage, crack and looseness of parts.	×	—
High temperature and high humidity	Exposed at 60 ± 2 °C, Relative humidity 90 to 95 %, 1000 h.			×	—
Damp heat, cyclic	Exposed at -10 to +65 °C, Relative humidity 90 to 96 %, 10 cycles, Total 240 h.		① Contact resistance : 50 mΩ MAX. ② Insulation resistance : 1 MΩ MIN. (At high humidity) ③ Insulation resistance : 50 MΩ MIN. (At dry) ④ No damage, crack and looseness of parts.	×	—
Dry heat	Exposed at 125 ± 2 °C, 1000 h.			×	—
Cold	Exposed at -55 ± 3 °C, 1000 h.		① Contact resistance : 50 mΩ MAX. ② No damage, crack and looseness of parts.	×	—
Sulphur dioxide [JIS C 60068-2-42]	Exposed at 40 ± 2 °C, Relative humidity 80 ± 5 %, 25 ± 5 ppm for 96 h.			×	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
△	1	DIS-F-00018569	YT. NINOMIYA	HS. HIRAHARA	20230621
REMARK			APPROVED	KN. SHIBUYA	20210519
			CHECKED	HH. MURAKAMI	20210519
			DESIGNED	RT. IKEDA	20210519
			DRAWN	RT. IKEDA	20210519
Unless otherwise specified, refer to IEC 60512.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-395622-05-00
△	HRS	SPECIFICATION SHEET	PART NO.	FH75M-**S-0. 4SH (05)	
		HIROSE ELECTRIC CO., LTD.	CODE NO.	CL580	△

SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
Resistance to soldering heat	1) Reflow soldering (To be 2 times MAX.) Peak TMP. 250 °C MAX. Reflow TMP. over 230 °C within 60 sec. Pre-heating. 150 to 200 °C 90 to 120 sec. 2) Soldering irons : 400 ± 10 °C, for 5 ± 1 sec.	No deformation of case of excessive looseness of the terminals.	×	—	
Solderability	Soldered at solder temperature, 245 ± 3 °C for immersion duration, 3 ± 0.3 sec.	A new uniform coating of solder shall cover a minimum of 95 % of the surface being immersed.	×	—	
<p>(note 1)</p> <p>Stabilize the FPC to PCB or something fixed, if pull-up or pull-down force is expected to be applied to the FPC.</p> <p>There's a case witch FPC retention force doesn't fulfill the value, because FPC specification affects the result of FPC retention force.</p>					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-395622-05-00
	SPECIFICATION SHEET		PART NO.	FH75M-**S-0. 4SH (05)	
	HIROSE ELECTRIC CO., LTD.		CODE NO	CL580	 2/2