

	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△1	13	RE-6-3467	LGO	JHW	24.02.22						
APPLICABLE STANDARD											
RATING	OPERATING TEMPERATURE RANGE		-55℃ TO +85℃(note1)			STORAGE TEMPERATURE RANGE		-10℃ TO +60℃			
	VOLTAGE		△ 50 V AC/DC			APPLICABLE CONNECTOR		BK13C06-16DS/2-0.35V(**)			
	CURRENT		SIGNAL CONTACT 0.3A POWER CONTACT 5.0A								
SPECIFICATIONS											
ITEM			TEST METHOD				REQUIREMENTS			QT	AT
CONSTRUCTION											
GENERAL EXAMINATION		CONFIRMED VISUALLY AND BY MEASURING INSTRUMENT.				ACCORDING TO DRAWING.			X	X	
MARKING		CONFIRMED VISUALLY.							X	X	
ELECTRICAL CHARACTERISTICS											
CONTACT RESISTANCE		20mV AC OR LESS 1kHz, 1mA				△1 SIGNAL CONTACT : 50mΩ MAX △1 POWER CONTACT : 15mΩ MAX			X	-	
INSULATION RESISTANCE		100V DC				50MΩ MIN			X	-	
VOLTAGE PROOF		△1 150V AC FOR 1min.				NO FLASHOVER OR BREAKDOWN			X	-	
MECHANICAL CHARACTERISTICS											
MECHANICAL OPERATION		△1 30 TIMES INSERTIONS AND EXTRACTIONS.				① CONTACT RESISTANCE: △1 SIGNAL CONTACT : 50mΩ MAX △1 POWER CONTACT : 15mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PATRS.			X	-	
VIBRATION		FREQUENCY 10 TO 55 TO 10 Hz, APPROX 5min SINGLE AMPLITUDE 0.75mm, 10CYCLES, FOR 3 DIRECTIONS.				① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-	
SHOCK		490 m/s² DURATION OF PULSE 11ms AT 3 TIMES FOR 3 DIRECTIONS.				① NO ELECTRICAL DISCONTINUITY OF 1μs. ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-	
ENVIRONMENTAL CHARACTERISTICS											
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → +85℃ TIME 30 → 30 min UNDER 5 CYCLES. (RELOCATION TIME TO CHAMBER: WITHIN2~3 MIN)				① CONTACT RESISTANCE: △1 SIGNAL CONTACT : 50mΩ MAX △1 POWER CONTACT : 15mΩ MAX ② INSULATION RESISTANCE : 50MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-	
DAMP HEAT (STEADY STATE)		EXPOSED AT 40±2℃, 90 TO 95%, 96h.				① CONTACT RESISTANCE: △1 SIGNAL CONTACT : 50mΩ MAX △1 POWER CONTACT : 15mΩ MAX ② INSULATION RESISTANCE : 25MΩ MIN ③ NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-	
SULPHUR DIOXIDE		EXPOSED IN 25 PPM FOR 96h, 25℃, 75±5%RH. (Test standard : JIS C 60068)				① CONTACT RESISTANCE: △1 SIGNAL CONTACT : 50mΩ MAX △1 POWER CONTACT : 15mΩ MAX ② NO DAMAGE, CRACK OR LOOSENESS OF PARTS.			X	-	
REMARKS Note 1 : INCLUDE THE TEMPERATURE RISING BY CURRENT.					DRAWN G.H.LEE 22.10.06	DESIGNED G.H.LEE 22.10.06	CHECKED H.W.JO 22.10.06	APPROVED H.W.JO 22.10.06	RELEASED ENG 22.10.06 DEPT		
Unless otherwise specified, refer to JIS C 5402 and IEC 60512											
Note QT: QUALIFICATION TEST AT: ASSURANCE TEST X: APPLICABLE TEST											
HIROSE KOREA CO.,LTD.				SPECIFICATION SHEET				PART NO. BK13C06-16DP/2-0.35V(895)			
CODE NO.(OLD)			DRAWING NO. ELC4-633200-95			CODE NO. CL 6665-0043-8-895			1 1		