

Jul.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-35°C TO +85°C(NOTES 1)	STORAGE TEMPERATURE RANGE	-10°C TO +60°C(NOTES 3)	
	OPERATING HUMIDITY RANGE	20% TO 80%(NOTES 2)	STORAGE HUMIDITY RANGE	40% TO 70%(NOTES 2)(NOTES 3)	
	VOLTAGE	50V AC / DC	APPLICABLE CONNECTOR	DF80※-40S-0.5V(##)	
	CURRENT	0.5 A/PIN (NOTE4)	APPLICABLE CABLE	THIN COAXIAL CABLE (AWG#40~AWG#46) / DISCRETE CABLE (AWG#32~36)	
SPECIFICATIONS					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.		ACCORDING TO DRAWING.	X	X
MARKING	CONFIRMED VISUALLY.			X	X
ENVIRONMENTAL CHARACTERISTICS					
SULFUR DIOXIDE GAS	EXPOSED IN 25PPM , 25°C , 75%RH , 96h.		NO DEFECT SUCH AS CORROSION WHICH IMPAIRS THE FUNCTION OF CONNECTOR.	X	—
RESISTANCE TO SOLDERING HEAT	①BONDING TEMPERATURE: 270°C MAX :5 sec MAX 200°C MIN :30 sec MAX ②MANUAL SOLDERING TEMPERATURE: 350°C, 3sec MAX.		NO DEFORMATION OF CASE OF EXCESSIVE LOOSENESS OF THE TERMINALS.	X	—
SOLDERABILITY	SOLDERED AT SOLDER TEMPERATURE, 245°C FOR INSERTION DURATION, 5 sec. (Sn-3.0Ag-0.5Cu)		SOLDER SHALL COVER A MINIMUM OF 95 % OF THE SURFACE BEING IMMERSSED.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
REMARKS			APPROVED	TS. SAKATA	12. 02. 15
NOTE1: INCLUDE THE TEMPERATURE RISING BY CURRENT			DRAWN	IO. DENPOUYA	12. 02. 15
NOTE2: NON CONDENSING					
NOTE3: THE TERM "STORAGE" REFERS TO PRODUCTS STORED FOR A LONG PERIOD PRIOR TO MOUNTING AND USE. THE OPERATING TEMPERATURE AND HUMIDITY RANGE COVERS THE NON-CONDUCTING CONDITION OF CONNECTORS AFTER BOARD MOUNTING AND THE TEMPORARY STORAGE CONDITIONS OF TRANSPORTATION, etc					
NOTE4: TEMPERATURE RISE OF CONNECTOR BODY ONLY, AND THAT OF CASE IS NOT INCLUDED. RATED CURRENT VARIES DEPENDING ON CABLES ASSEMBLED.					
Unless otherwise specified, refer to JIS C 5402,IEC60512.					
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-335921-01	
	SPECIFICATION SHEET		PART NO.	DF80-40P-SHL	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL662-8003-8-00	1/1