

APPLICABLE STANDARD					
Rating	Operating Temperature range	-55 °C to 85 °C <sup>(1)</sup>	Operating Humidity range	Relative humidity 95 % MAX <sup>(3)</sup>	
	Voltage	50 V AC	Storage Temperature range	-10 °C to 60 °C <sup>(2)</sup>	
	Current	0.3 A	Storage Humidity range	40 % to 70 % <sup>(2)</sup>	
SPECIFICATIONS					
ITEM	TEST METHOD	REQUIREMENTS	QT	AT	
<b>CONSTRUCTION</b>					
General examination	Visually and by measuring instrument.	According to drawing.	×	×	
Marking	Confirmed visually.		×	×	
<b>ELECTRIC CHARACTERISTICS</b>					
Contact resistance	100 mA (DC OR 1000 Hz)	60 mΩ MAX .	×	—	
Insulation resistance	100 V DC.	100 MΩ MIN.	×	—	
Voltage proof	150 V AC for 1 min.	No flashover or breakdown.	×	×	
<b>MECHANICAL CHARACTERISTICS</b>					
Insertion and withdrawal forces	Measured by applicable connector.	Insertion force : 72.0 N MAX. Withdrawal force: 3.0 N MIN.	×	—	
Mechanical operation	50 Times insertions and extractions.	1)Contact resistance: 70 mΩ MAX. 2)No damage, crack and looseness of parts.	×	—	
Vibration	Frequency 10 to 55 to 10 Hz, Single amplitude: 0.75 mm, 10 cycles for 3 axial directions.	1)No electrical discontinuity of 1 μs. 2)No damage, crack and looseness of parts.	×	—	
Shock	490 m/s <sup>2</sup> , Duration of pulse 11 ms at 3 times for 3 both axial directions.		×	—	
<b>ENVIRONMENTAL CHARACTERISTICS</b>					
Damp heat (Steady state)	Exposed at 40 ± 2 °C, 90 to 95 %, 96 h.	1)Contact resistance : 70 mΩ MAX. 2)Insulation resistance: 100 MΩ MIN. 3)No damage, crack and looseness of parts.	×	—	
Rapid change of temperature	Temperature: -55 → +85 °C Time : 30 → 30 min. Under 5 cycles. (Relocation time to chamber:Within 2 to 3 min)		×	—	
Cold	Exposed at -55 °C, 96 h	1)Contact resistance : 70 mΩ MAX. 2)No damage, crack and looseness of parts.	×	—	
Dry heat	Exposed at +85 °C, 96 h		×	—	
Corrosion salt mist	Exposed in 5 % salt water spray for 48 h.	1)Contact resistance : 70 mΩ MAX. 2)No heavy corrosion.	×	—	
Sulfur dioxide	Exposed 10 ppm, 40 °C, 75 ± 5 % for 96 h. (Test standard:JIS C 60068)		×	—	
Resistance to soldering heat	1)Reflow soldering: Peak TMP : 250 °C MAX Reflow TMP: 220 °C MIN for 60sec. 2)Soldering irons: 360 °C MAX for 5 sec.	No deformation of case of excessive looseness of the terminal.	×	—	
Solderability	Soldered at solder temperature 240 ± 3 °C for immersion duration, 3 sec.	A new uniform coating OF solder shall cover a minimum of 95 % of the surface being immersed.	×	—	
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
REMARKS	(1)Temperature rise included when energized. (2)This storage indicates a long-term storage state for the unused product before the board mounted. (3)NON-Condensing. Unless otherwise specified, refer to IEC-60512.		APPROVED	NH. NAKATA	17. 11. 22
			CHECKED	HT. YAMAGUCHI	17. 11. 22
			DESIGNED	MT. ITANO	17. 11. 21
			DRAWN	MT. ITANO	17. 11. 21
Note	QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC-362078-83-00	
<b>HRS</b>	SPECIFICATION SHEET		PART NO.	FX10A-120P-SV4 (83)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL570-0061-7-83	△ 1/1