









Oct.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.




Recommended PCB Layout
(Board thickness : t=1.6±0.1mm)



Mating Figure(1:1)



Packaging Figure (3PINs)
(FREE)



- Note 1. 96 Pieces / Tray
 2. Refer to the technical specification (ETAP-H0816-00) for the packaging type.
 3. Refer to the technical specification (ETAP-H0654-00) in handling this product.
 4. UL (File No. E52653)
 C-UL (File No. E52653)
 TÜV (Certificate No. R50400864) authorization article.



1	PBT	BLACK, UL94-V0	3	PS	White
2	Copper Alloy		2	Copper Alloy	Contact area : Au plating 0.2µmMIN Lead area : Sn plating 1µmMIN Under plating : Ni plating 1µmMIN
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2:1	COUNT 1	DESCRIPTION OF REVISIONS DIS-H-00020310	
DESIGNED TS. KUMAZAWA		CHECKED SZ. ONO		DATE 2024. 04. 04	
APPROVED : SJ. OKAMURA 2022. 08. 04		DRAWING NO. EDC-386586-50-00			
CHECKED : TT. OHSAKO 2022. 08. 04		PART NO. DF60F-2P-10.16DSA (50)			
DESIGNED : SN. MIWA 2022. 08. 02		CODE NO. CL0680-4007-0-50			
DRAWN : SN. MIWA 2022. 08. 02					



HIROSE ELECTRIC CO., LTD.