

APPLICABLE STANDARD					
RATING	Operating Temperature Range	-55°C to 125°C(Notes 1)	Storage Temperature Range	-10°C TO 60°C	
	Voltage	30V AC/DC	Mating Connector	DF40TC-120DP-0.4V (**)	
	Current	0.3A			
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
General Examination		Visually and by measuring instrument.	① According to drawing.	X	X
Marking.		Confirmed visually.		X	X
ELECTRIC CHARACTERISTICS					
Contact Resistance	20mV AC or less 1kHz, 1mA.		① 90mΩ MAX.	X	—
Insulation Resistance	100V DC.		① 50MΩ MIN.	X	—
Voltage Proof	100V AC for 1 min.		① No flashover or breakdown.	X	—
MECHANICAL CHARACTERISTICS					
Mechanical Operation	10times insertions and extractions.		① Contact resistance: 90mΩ MAX. ② No damage, crack or looseness of parts.	X	—
Vibration	Frequency 10 to 500Hz, acceleration 49 m/s ² Sweep time 11min(1 oct/min.) 8h for 3 axial directions.		① No electrical discontinuity of 1 μs. ② No damage, crack or looseness of parts.	X	—
Shock	Acceleration 980 m/s ² , duration of pulse 6 ms at 3 times for 3 directions.			X	—
ENVIRONMENTAL CHARACTERISTICS					
Rapid Change of Temperature	Temperature -55 → 125 °C Time 30 → 30 min Under 1000 cycles.		① Contact resistance: 90mΩ MAX. ② No damage, crack or looseness of parts.	X	—
Dry Heat	Exposed at 125 °C, 1,000 h.			X	—
Damp Heat	Exposed at 60 ± 2 °C Relative humidity 90 to 95 %, 1000 h.		① Contact resistance: 90mΩ MAX.	X	—
Damp Heat, Cyclic	Exposed at -10 to 65°C, Relative humidity 90 to 96%, 10cycles, total 240h.		② Insulation resistance: 25 MΩ MIN. ③ No damage, crack or looseness of parts.	X	—
Sulfur Dioxide	Exposed in 25 PPM for 96h, 40°C, Relative humidity 80%.		① Contact resistance: 180mΩ MAX.	X	—
Heat Resistance of Soldering	Recommended temperature profile soldering area MAX 250°C, 220°C for 60 seconds MAX. Preheating area 150 to 180°C 90 to 120 seconds. Maximum twice action is allowed under the same condition. Recommended manual soldering condition Soldering iron temperature 350°C. Soldering time: within 3 seconds.		① No deformation of case of excessive looseness of the terminals.	X	—
Solderability	Soldering temperature: 245 ± 5°C Duration of immersion: soldering for 3±0.5 seconds.		A new uniform coating of solder shall cover a minimum of 95% of the surface being immersed.	X	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
⚠	2	DIS-H-00015139	YK. SATAKE	RT. SHIMIZU	20220905
REMARKS			APPROVED	WR. FUKUCHI	20211025
Note1: Include the temperature rising by current			CHECKED	YK. SATAKE	20211025
			DESIGNED	RH. KAGAMI	20211025
			DRAWN	RH. KAGAMI	20211025
Unless otherwise specified, refer to JIS C 5402. IEC 60512.					
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC-397837-88-00
HRS	SPECIFICATION SHEET		PART NO.	DF40TC-120DS-0.4V (88)	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL0684-4296-0-88	⚠ 1/1