







May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT



RECOMMENDED PCB PATTERN



NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW
(REFER TO RIGHT FIG.)
USED REFLOW SYSTEM

NO. OF CYCLES : 1R IN THE AIR OR NITROGEN
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C
90~120s


2. TEMPERATURE FOR SOLDERING IRON
: 280~300°C WITHIN 2s

3. CO-PLANARITY SHALL BE 0.1mm MAX.

4. RECOMMENDED PCB THICKNESS IS 1.6mm.

5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.

6. [Pattern] : PROHIBITED PATTERN AREA





3	BRASS	SURFACE PLATING : TIN PLATING 1μm min UNDER PLATING : NICKEL 1μm min			
2	BRASS	SURFACE PLATING : TIN PLATING 1μm min UNDER PLATING : NICKEL 1μm min	6	POLYESTER	
1	PA	BLACK UL94V-0	5	POLYSTYRENE	
			4	POLYIMIDE	PICK & PLACE TAPE
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED CHECKED DATE
HIROSE ELECTRIC CO., LTD.		APPROVED : HK. UMEHARA	20190517	DRAWING NO.	EDC-376618-00-00
		CHECKED : OM. MIYAMOTO	20190517	PART NO.	ZE05H-8DP-2V
		DESIGNED : TY. ISHIGURO	20190517	CODE NO.	CL752-2312-0-00
		DRAWN : GYEONGMIN LEE	20190515		

May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


PACKING STYLE

REEL DIMENSION

PACKING STYLE DRAWING



CARDBOARD DIMENSION (FREE)



W=(405) (mm)
D=(405) (mm)
H= (51) (mm)

HRS	DRAWING NO.	EDC-376618-00-00
	PART NO.	ZE05H-8DP-2V
	CODE NO.	CL752-2312-0-00
		$\triangle$ 2/2