









Jun.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

ELV, RoHS COMPLIANT



- NOTE 1. RECOMMENDED TEMPERATURE PROFILE FOR REFLOW (REFER TO RIGHT FIG.)
USED REFLOW SYSTEM : IR IN THE AIR OR NITROGEN
NO. OF CYCLES : 2 MAX
PEAK : 250°C
OVER 230°C : 20~40s
PREHEAT : 150~180°C 60~120s
2. TEMPERATURE FOR SOLDERING IRON : 280~300°C WITHIN 2s
3. CO-PLANARITY SHALL BE 0.1mm MAX.
4. RECOMMENDED PCB THICKNESS IS 1.6mm.
5. RECOMMENDED SOLDER THICKNESS IS 0.15mm.



TRAY PACKING SPECIFICATIONS

6 TRAYS STACKING.
ODD NUMBER TRAYS AND EVEN NUMBER TRAYS ARE REVERSE DIRECTION.
TOP TRAY IS EMPTY.

CARDBOARD PADS
EMPTY TRAY
CARTON
PP BAND
6TRAYS
330
44.1
P=34.54
133
240
343
225
61.8
P=41.8
32PCS PER TRAY.
PACK QUANTITY: 160PCS PER CARTON.

2	BRASS	TIN PLATING T=0.64	4	BRASS	TIN PLATING T=0.4
1	PPS	BLACK	3	BRASS	TIN PLATING T=0.64
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED CHECKED DATE
		APPROVED : HK. UMEHARA	20200928	DRAWING NO.	EDC-169257-60-00
		CHECKED : HH. TSUKUMO	20200927	PART NO.	GT25H-12DP-2.2V(60)
		DESIGNED : DONGCHAN KIM	20200924	CODE NO.	CL775-0050-9-60
		DRAWN : AN. SAIKI	20200917		