

Features


- 1 Ultra Low profile 1.18mm height
- 2 Incorrect card insertion prevention
- 3 Card fly-out prevention
- 4 Card detection switch
- 5 Easy inspection with exposed contact design




The world's
lowest profile
in its Class
1.18 mm

*As push-push type
micro SIM card connector
as of Feb. 2017

Dimensions



Prevents card fly-out



⇒ Holds nano SIM securely in place

Specifications

Rated Current	0.5A
Rated Voltage	10V AC
Operating Temperature	-30 to +85°C
Contact Resistance	100mΩ Max.
Withstanding Voltage	500V AC for 1 minute
Insulation Resistance	1,000MΩ Min. (500V DC)
Mating cycles	5,000 times

• RoHS compliant, Halogen-free product*

*This product satisfies halogen-free requirements defined as 900ppm maximum chlorine, 900ppm maximum bromine, and 1,500ppm maximum total of chlorine and bromine.

※ Please contact Hirose's sales representative prior to adopting the products to in-vehicle devices.