







ELV. RoHS COMPLIANT

A-A




Packing specification

(1) After placing parts in trays, stack in five layers.
(Top layer will be empty.)




(2) Place bound trays in box,
then place cardboard sheet on top.

(3) Using packing tape, affix sheet of
cardboard to box in four places.




(4) Place lid on box and seal with packing tape.

W=(368)mm
D=(278)mm
H=(261)mm



HOUSING ASSY
(1:1)



Note 1. Counter part is HVH-280-2/2P-HU(CL778-0500-0-00)
2. Following parts are available.
HOLDER : HVH-280-2/2S-HO(CL778-0507-0-00)
WIRE SEAL : HVH-280-2/2S-WS(CL778-0505-0-00)
POWER CRIMP CONTACT : HVH-280-1214SCF(CL778-0502-0-00)
SHIELD CONTACT : HVH-280-4.2CF(CL778-0503-0-00)
3. Assembly procedure refer to ETAD-T0574-00
4. Black spots could be observed on the surface of Housing,
but it does not affect the product quality.

3	PBT	RED. UL94 V-0							
2	SUS	SURFACE:TIN PLATING 1μm MIN UNDER PLATING:NICKEL PLATING 0.5μm MIN	5	COPPER ALLOY	SURFACE:TIN PLATING 1μm MIN UNDER PLATING:NICKEL PLATING 0.5μm MIN				
1	PBT	ORANGE. UL94 V-0	4	SILICONE	BLUE				
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS				
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-T-00016953	DESIGNED TS. SHIMIZU	CHECKED TY. MOGI	DATE 20230327		
		APPROVED : HK. UMEHARA	20161128	DRAWING NO.	EDC-369972-00-00				
		CHECKED : HK. UMEHARA	20161128	PART NO.	HVH-280-2/2S-HU				
		DESIGNED : KO. NAKAMURA	20161128	CODE NO.	CL0778-0504-0-00				
		DRAWN : KO. NAKAMURA	20161128						