


May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes 1 Rotation examples of ref. No. ① and ⑤ are shown.  
2 Across flats of hexagon hole of ref. No. ⑧ to be 1.27.  
The recommended tightening torque of ref. No. ⑧ to be 0.3 to 0.4 N·m.  
3 The recommended tightening torque of ref. No. ⑤ to be 2 to 3 N·m.  
4 LOCTITE 243, HENKEL JAPAN or equivalent is recommended to prevent ref. No. ①, ⑦ and ⑧ from loosening.  
5 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. Please confirm before the use.

4	PPS	(BLACK) UL94V-0	8	STEEL	NICKEL PLATING	Hexagon socket set screws M2.6×0.45×2
3	PPS	(BLACK) UL94V-0	7	BRASS	NICKEL PLATING	
2	COPPER ALLOY	SILVER PLATING 5μm min	6	ZINC ALLOY	MATTE FINISH NICKEL PLATED	
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	5	ZINC ALLOY	MATTE FINISH NICKEL PLATED	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS	
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED
APPROVED : HY. KOBAYASHI 15.11.19				DRAWING NO. EDC-006812-81-00		
CHECKED : HY. KOBAYASHI 15.11.19				PART NO. RM12BJB-6S(81)		
DESIGNED : KN. IKEHARA 15.11.19				CODE NO. CL109-0642-3-81		
DRAWN : KN. IKEHARA 15.11.19						