






△ (Change Orientation)

Panel cutout △
t: 0.5~2



Note 1 The tightening torque of Ref. No. ⑤: 2 to 2.5 N·m.
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion (M14×0.75) of Ref. No. ① in order to prevent loosening.

3	Polyphenylene sulfide	(BLACK)	6	Phosphor bronze	Nickel plating
2	Copper alloy	Silver plating 2μm min.	5	Brass	Nickel plating
1	Zinc alloy	Matte finish nickel plated	4	Polyphenylene sulfide	(BLACK)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT △ 1	DESCRIPTION OF REVISIONS DIS-C-00016516	DESIGNED TY. SUZUKI
HIROSE ELECTRIC CO., LTD.		APPROVED : TP. KOMATSU	20230509	DRAWING NO. EDC-027507-81-00	DATE 20231113
		CHECKED : HY. KOBAYASHI	20230509	PART NO. RM12BRD-2PH(81)	
		DESIGNED : HT. ZENBA	20230509	CODE NO. CL0109-0823-8-81	
		DRAWN : KR. SUZUKI	20230508		
△ 1/1					