




- Notes ① The recommended clamp torque of ref. No. ⑩ : 0.2 to 0.3 N·m.
LOCTITE 243, HENKEL JAPAN or equivalent is recommended to prevent ref.No.⑩ from loosening.
② Rotation of ref. No. ⑥ to ref. No. ① is shown.
③ The cable pull and twisting strength and other characteristics may differ, depending on the cable structure.
Please confirm before the use.

5	BRASS	NICKEL PLATING	10	BRASS	NICKEL PLATING	M2.6×0.45×2
4	PPS	(BLACK) UL94V-0	9	PHOSPHOR BRONZE	NICKEL PLATING	
3	PPS	(BLACK) UL94V-0	8	BRASS	NICKEL PLATING	JIS B 1101 M2×0.4×10
2	COPPER ALLOY	SILVER PLATING 2 μm.	7	BRASS	NICKEL PLATING	
1	BRASS	NICKEL PLATING	6	BRASS	NICKEL PLATING	
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS	
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00000841	DESIGNED KN. IKEHARA	CHECKED HY. KOBAYASHI
DATE 16. 03. 02		APPROVED : HY. KOBAYASHI 15. 11. 06		DRAWING NO. EDC-028025-81-00		
CHECKED : HY. KOBAYASHI 15. 11. 06		DESIGNED : KN. IKEHARA 15. 11. 06		PART NO. RM15TP-4SA(81)		
DRAWN : KN. IKEHARA 15. 11. 06				CODE NO. CL109-0846-3-81		