



- Notes ① The tightening torque of Ref. No. ⑦: 3 to 4 N·m.
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion (M21×1) of Ref. No. ① in order to prevent loosening.
- ② When mounted on chassis, be careful that Ref.No.⑤ is fitted into the indicated groove without any biting.
- ③ Surface:Gold plating 0.2μm min.
Under :Nickel plating 3μm min.

4	Polyphenylene sulfide	(Black)			
3	Polyphenylene sulfide	(Black)	7	Brass	Nickel plating
2	Brass	③	6	Phosphor bronze	Nickel plating
1	Zinc alloy	Chrome plating	5	Silicone rubber	(Black)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00016536	DESIGNED TY. SUZUKI
		APPROVED : TP. KOMATSU	20230613	DRAWING NO.	EDC-110769-82-00
		CHECKED : HY. KOBAYASHI	20230613	PART NO.	RM15WTRZA-4P(82)
		DESIGNED : HT. ZENBA	20230613	CODE NO.	CL0109-1653-5-82
		DRAWN : KR. SUZUKI	20230613		
				DATE	20231208
				CHECKED	HY. KOBAYASHI