



- Notes:
- 1 Applicable crimping: SR30-PC(L103-0266-5-00), separately.
  - 2 Rotation torque resistance of ref. NO. ① and No. ③ are approx. 0.7 N·m.
  - 3 The recommended clamp torque of ref. No. ⑤: 1.5 N·m.
  - 4 The recommended clamp torque of ref. No. ⑦: 0.1 to 0.15 N·m.
  - 5 LOCTITE 243, HENKEL JAPAN or equivalent is recommended to prevent ref. No. ① and No. ⑦ from loosening.
  - 6 Rotation examples of ref. No. ① and No. ⑤ are shown.
  - 7 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. Please confirm before the use.

4	Polytetrafluoroethylene	(White)			
3	Polyacetal	(White)	7	Steel	Nickel plating JIS B 1117 M2. 6×0.45×3
2	Phosphor bronze	Surface: Gold plating 0.2μm min. Under: Nickel plating 3μm min.	6	Chloroprene rubber	(Black)
1	Brass	Chrome plating	5	Brass	Nickel plating
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
APPROVED : SU. OBARA 16. 03. 25				DRAWING NO. EDC-005968-72-00			
CHECKED : HY. KOBAYASHI 16. 03. 25				PART NO. SR30-10JE-6S<72>			
DESIGNED : DS. MATSUNE 16. 03. 25				CODE NO. CL103-0259-0-72			
DRAWN : DS. MATSUNE 16. 03. 25							