




- NOTES: ① THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑤: 1.5N·m
② THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑨: 0.1~0.15N·m
③ LOCTITE 243, LOCTITE OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ⑤ AND NO. ⑨ FROM LOOSENING.
4 ROTATION EXAMPLES OF REF. NO. ① AND NO. ⑤ ARE SHOWN.
5 THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE, PLEASE CONFIRM BEFORE THE USE.

5	BRASS	NICKEL PLATING	10	BRASS	
4	FLUORO		9	STEEL	NICKEL PLATING JIS B 1117 M2.6X0.45X3 SLOTTED SET SCREWS
3	POLYACSTAL		8	BRASS	CHROME PLATING
2	BRASS	SURFACE PLATING: GOLD PLATING 0.2µm min. UNDER PLATING: NICKEL PLATING 3µm min.	7	BRASS	CHROME PLATING
1	ZINC ALLOY	NICKEL PLATING	6	CR	(BLACK)
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS
UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED
					CHECKED
					DATE
HIROSE ELECTRIC CO., LTD.		APPROVED : HY. KOBAYASHI	18.02.22	DRAWING NO.	EDC-006634-31-00
		CHECKED : HY. KOBAYASHI	18.02.22	PART NO.	SR30-10PG-6P<31>
		DESIGNED : TH. KAMEYA	18.02.21	CODE NO.	CL103-0273-0-31
		DRAWN : TH. KAMEYA	18.02.21		