




- Notes
- 1 Rotation example of Ref. No. ① and ⑤ are shown.
 - ② The tightening torque of Ref. No. ⑤: 2 to 3 N · m.
 - ③ The tightening torque of Ref. No. ⑧: 0.2 to 0.3 N · m.
Across flats hexagon head of Ref. No. ⑧: 1.27
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion of Ref. No. ⑧ in order to prevent loosening.
 - ④ The tightening torque of Ref. No. ⑦: 0.12 to 0.15 N · m.
Apply Loctite 243 HENKEL JAPAN or equivalent to the threaded portion of Ref. No. ⑦ in order to prevent loosening.
 - 5 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure, please confirm before the use.

4	Polyphenylene sulfide	(Black)	8	Steel	Nickel plating
3	Polyphenylene sulfide	(Black)	7	Brass	Nickel plating
2	Copper alloy	Silver plating 5 μm min.	6	Zinc alloy	Matte finish nickel plated
1	Zinc alloy	Matte finish nickel plated	5	Zinc alloy	Matte finish nickel plated
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 1	DESCRIPTION OF REVISIONS DIS-C-00016538	DESIGNED TY. SUZUKI	CHECKED HY. KOBAYASHI	DATE 20240201
-------------	--	----------------	------------	--	------------------------	--------------------------	------------------

HRS HIROSE ELECTRIC CO., LTD.	APPROVED : TP. KOMATSU	20230612	DRAWING NO.	EDC-006967-81-00	
	CHECKED : HY. KOBAYASHI	20230612	PART NO.	RM12BJB-7S(81)	
	DESIGNED : HT. ZENBA	20230609	CODE NO.	CL0109-0643-6-81	
	DRAWN : KR. SUZUKI	20230607			