





Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- 1 Across flats hexagon head of REF. NO. ⑧: 1.27
The concave portion with REF. NO. ⑨ clamped to the cable.
The recommended tightening torque, REF. NO. ⑧: 0.3 to 0.4 N·m.
LOCTITE 263, HENKEL JAPAN or equivalent is recommended to prevent REF. NO. ⑧ for loosening.
 - 2 The recommended tightening torque, REF. NO. ⑦: 2 to 2.5 N·m.
LOCTITE 263, HENKEL JAPAN or equivalent is recommended to prevent REF. NO. ⑦ for loosening.
 - 3 Applicable crimping tool of REF. NO. ⑨: HR10A-TC-03(CCL150-0057-2)
 - 4 One example of the rotation of REF. NO. ⑦ to REF. NO. ① is shown.
 - 5 The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. Please confirm before the use.

5	Polyamide	(Black) UL94V-0	10	Chloroprene rubber	(Black)
4	Phosphor bronze	Gold plating 0.2μm min.	9	Brass	
3	Phosphor bronze	Nickel under plating 2μm min.	8	Steel	Nickel plating M2.6×0.45×3
2	Stainless steel		7	Brass	Matte finish nickel plate
1	Zinc alloy	Matte finish nickel plated	6	Brass	Matte finish nickel plate
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
 HIROSE ELECTRIC CO., LTD.				APPROVED :EJ. KUNII 15. 09. 09	DRAWING NO.	EDC-042036-74-74	
				CHECKED :EJ. KUNII 15. 09. 09	PART NO.	HR10A-10JE-12P(74)	
				DESIGNED :TP. KOMATSU 15. 09. 09	CODE NO.	CL110-0450-2-74	
				DRAWN :TP. KOMATSU 15. 09. 09			