

| | | | | | |
|--|--|---------------------------------------|---|-----------------|------------------|
| APPLICABLE STANDARD | | | | | |
| RATING | Operating temperature range. | -25°C to +85°C | Storage temperature range. | -10°C to +60°C | |
| | _____ | _____ | _____ | _____ | |
| | _____ | _____ | _____ | _____ | |
| SPECIFICATIONS | | | | | |
| ITEM | | TEST METHOD | REQUIREMENTS | QT | AT |
| CONSTRUCTION | | | | | |
| General examination. | | Visually and by measuring instrument. | According to drawing. | X | X |
| Marking | | Confirmed visually | | X | X |
| ENVIRONMENTAL CHARACTERISTICS | | | | | |
| Rapid change of temperature | Temperature -55→ R/T ⁽¹⁾ → +85 → R/T °C Time 30 → 2 TO 3 → 30 → 2 TO 3 min under 5 CYCLES. | | No damage.crack and looseness of parts. | X | - |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| | | | | | |
| COUNT | DESCRIPTION OF REVISIONS | | DESIGNED | CHECKED | DATE |
| ① | | | | | |
| REMARK | | | APPROVED | EJ.KUNII | 15.09.29 |
| | | | CHECKED | EJ.KUNII | 15.09.29 |
| | | | DESIGNED | TP.KOMATSU | 15.09.29 |
| | | | DRAWN | TP.KOMATSU | 15.09.29 |
| Unless otherwise specified, refer to IEC 60512. | | | | | |
| Note QT:Qualification Test AT:Assurance Test X:Applicable Test | | | DRAWING NO. | | ELC-042417-00-00 |
| HRS | SPECIFICATION SHEET | | PART NO. | HR10A-13R-C | |
| HIROSE ELECTRIC CO., LTD. | | | CODE NO. | CL110-0452-8-00 | ⚠ 1/1 |