



1			2			3			4		
	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE		COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					.	△					.
△					.	△					.
△					.	△					.



- NOTE 1 APPLICABLE CONTACT : HR12-SC-212  
APPLICABLE WIRE : AWG#26~30 ( INSULATOR OUTER DIA. OF  $\phi$  1 OR LESS )  
APPLICABLE TOOL, EXTRACTPR : HR12-SC-TP
- 2 THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑤ : 1.5N · m .  
LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT  
REF. NO. ⑤ FROM LOOSENING.

3	PBT	(BLACK) UL94V-0			
2	STAINLESS STEEL		5	BRASS	NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	4	PHOSPHOR BRONZE	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD) CL			DRAWN	DESIGNED	CHECKED
			H.Kishi '05.08.29	H.Kishi '05.08.29	E. Kuma '05.08.30
					M. Sato '05.08.30
DRAWING NO.			PART NO.		
EDC4-021660-73			HR10A-7R-4SC(73)		
UNITS mm			CODE NO.		
 HIROSE ELECTRIC CO., LTD.			CL110-0506-5-73		