


Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

1		2			3			4		
COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	
△					△					
△					△					
△					△					



A DETAIL OF MOUNTING GUIDE

PANEL CUTOUT  
t 0.7~2

NOTE 1 APPLICABLE CONTACT : HR12-SC-212  
 APPLICABLE WIRE : AWG#26~30 ( INSULATOR OUTER DIA. OF φ 1 OR LESS )  
 APPLICABLE TOOL , EXTRACTPR : HR12-SC-TP  
 ② THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑤ : 1.5N · m .  
 LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT  
 REF. NO. ⑤ FROM LOOSENING.

3	PBT	(BLACK) UL94V-0			
2	STAINLESS STEEL		5	BRASS	NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	4	PHOSPHOR BRONZE	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS

CODE NO. (OLD)	CL	DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
		H.Kishi 05.08.29	H.Kishi 05.08.29	E. Hunii 05.08.30	M. Sato 05.08.30	

 SCALE 2 : 1 UNITS mm	DRAWING NO.	EDC4-021663-73	PART NO.	HR10A-7R-6SC(73)
	 HIROSE ELECTRIC CO.,LTD.	CODE NO.	CL110-0508-0-73	1/1

In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.