

Oct.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△					△				
△					△				
<b>APPLICABLE STANDARD</b>									
RATING	OPERATING TEMPERATURE RANGE	-25 °C TO +85 °C			STORAGE TEMPERATURE RANGE	— °C TO — °C			
	VOLTAGE	AC — V . DC — V							
	CURRENT	2 A			APPLICABLE CABLE	AWG #26~#30 (INSULATION DIA φ1 MAX)			
<b>SPECIFICATIONS</b>									
ITEM		TEST METHOD			REQUIREMENTS			QT	AT
<b>CONSTRUCTION</b>									
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.			ACCORDING TO DRAWING.			○	○
MARKING		CONFIRMED VISUALLY.						○	○
<b>ELECTRIC CHARACTERISTICS</b>									
CONTACT RESISTANCE		CONTACT SHALL BE MEASURED AT DC 1 A			10 mΩ MAX.			○	○
		CONTACT SHALL BE MEASURED AT DC — A			— MΩ MAX.			—	—
<b>MECHANICAL CHARACTERISTICS</b>									
CONTACT INSERTION AND WITHDRAWAL FORCES		— BY STEEL GAUGE.			INSERTION AND WITHDRAWAL FORCES : — N MIN.			—	—
MECHANICAL OPERATION		1000 TIMES INSERTIONS AND EXTRACTIONS.			CONTACT RESISTANCE: 15 mΩ MAX.			○	—
					— RESISTANCE: — mΩ MAX.			—	—
TENSILE STRENGTH (CRIMPED CONNECTION)		CRIMPED ONLY CONDUCTOR OF THE APPLICABLE WIRE AND PULLING THE APPLICABLE WIRE.			(7/ φ0.1 )AWG #30 : 10 N MIN.			○	—
					(7/ φ0.12)AWG #28 : 16 N MIN.			○	—
					(7/ φ0.16)AWG #26 : 24 N MIN.			○	—
<b>ENVIRONMENTAL CHARACTERISTICS</b>									
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.			NO HEAVY CORROSION.			○	—
<b>REMARKS</b>					DRAWN	DESIGNED	CHECKED	APPROVED	RELEASED
					H. YOKOMIZO 98.6.30		<i>M. Yoshida</i> 98.7.4		
Unless otherwise specified, refer to JIS C 5402.									
Note QT:Qualification Test AT:Assurance Test O:Applicable Test									
<b>HR</b> HIROSE ELECTRIC CO., LTD.				SPECIFICATION SHEET			PART NO. HR10-PC-111		
CODE NO. (OLD)		DRAWING NO.			CODE NO.			1	1
CL		ELC4-025991			CL110-0515-6			1	1

TO  
R  
  
120

