


Nov.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- Notes
- ① Applicable crimp contact : HR10-PC-212 (CL110-0514-3)  
Applicable wire : AWG#26 TO #30  
(Covered wire MAX. Outside DIA. φ1)  
Applicable contact removal tool  
(Extraction tool) : RP6-SC-TP(CL150-0039-0)
  - ② Applicable crimping tool of REF. NO. ⑦ :  
HR10A-TC-02(CL150-0041-2)  
The hole diameter for crimping : φ7.0
  - ③ The recommended tightening torque, REF. NO. ⑤ : 2 to 2.5 N · m.
  - ④ Across flats hexagon head of REF. NO. ⑥ : 1.27  
The recommended tightening torque, REF. NO. ⑥ : 0.3 to 0.4 N · m.  
The concave portion with REF. NO. ⑦ clamped to the cable.
  - ⑤ LOCTITE 243, HENKEL JAPAN or equivalent is recommended to prevent REF. NO. ① and ⑥ for loosening.
  - ⑥ One example of the rotation of REF. NO. ⑤ to REF. NO. ① is shown.
  - ⑦ The cable pull and twisting strength and other characteristics may differ, depending on the cable structure. Please confirm before the use.

4	Brass	Matte finish nickel plated	8	Chloroprene rubber	(Black)
3	PBT	(BLACK) UL94V-0	7	Brass	
2	Stainless steel		6	Steel	Nickel plating M2.6X0.45X3
1	Zinc alloy	Matte finish nickel plated	5	Brass	Matte finish nickel plated
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
HIROSE ELECTRIC CO., LTD.		APPROVED : EJ. KUNII	14. 11. 08	DRAWING NO.	EDC4-025182-01			
		CHECKED : HY. KISHI	14. 11. 08	PART NO.	HR10A-10J-12PC(73)			
		DESIGNED : HN. TANAKA	14. 11. 08	CODE NO.	CL110-0611-0-73		1	1
		DRAWN : HR. SATO	14. 11. 07					