

NOTE 1 APPLICABLE CRIMP CONTACT:HR12-SC-212(CLI12-0408-9)

WIRE RANGE:AWG#26 TO 30(JACKET DIAMETER:φ1 MAX.)

APPLICABLE CRIMP CONTACT EXTRACTION TOOL:HR12-SC-TP(CLI150-0050-3)

② APPLICABLE CRIMP TOOL, REF. NO. ⑦:HR10A-TC-02(CLI150-0041-2)

APPLY TO φ5.3.

③ THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑤:1.5 TO 2N·m.

④ ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑥:1.27.

THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑥:0.3 TO 0.4N·m.

⑤ LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ①, ⑥ FOR LOOSENING.


⑥ ONE EXAMPLE OF THE ROTATION OF REF. NO. ① TO REF. NO. ⑤ IS SHOWN.

⑦ THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE.

PLEASE CONFIRM BEFORE THE USE.

4	BRASS	MATTE FINISH NICKEL PLATED	8	CHLOROPRENE RUBBER	(BLACK)
3	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0	7	BRASS	
2	STAINLESS STEEL		6	STEEL	NICKEL PLATING M2.6X0.45X2
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	5	BRASS	MATTE FINISH NICKEL PLATED
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS
mm



SCALE
2 : 1

COUNT
△

DESCRIPTION OF REVISIONS

DESIGNED

CHECKED

DATE

HRS

HIROSE
ELECTRIC
CO., LTD.

APPROVED :MO. SATOH

06.12.21

CHECKED :EJ. KUNII

06.12.20

DESIGNED :TO. HORII

06.12.19

DRAWN :MK. SATO

06.12.15

DRAWING
NO.

EDC4-021661-73

PART
NO.

HR10A-7J-4SC(73)

CODE
NO.

CL110-0510-2-73

△ 1/1