


May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

TO
R

NOTES 1 APPLICABLE CRIMP CONTACT:HR12-SC-212(CL112-0408-9)
APPLICABLE WIRE:AWG#26 TO #30(COVERED WIRE MAX,OUTSIDE DIA.φ 1)
APPLICABLE CONTACT REMOVAL TOOL(EXTRACTION TOOL):HR12-SC-TP(CL150-0050-3)
2 THE RECOMMENDED CLAMP TORQUE,REF.NO.③ :2 TO 2.5N·m.
LOCTITE 242,HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF.NO.③FOR LOOSENING.

COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS	BY	CHKD	DATE
△				..	△				..
△				..	△				..
△				..	△				..



2	POLYBUTYLENE TEREPHTHALATE (BLACK)	UL94V-0	4	PHOSPHOR BRONZE	NICKEL PLATING
1	BRASS	NICKEL PLATING	3	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS	NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD) CL			DRAWN M. Sato 07.03.20		
			DESIGNED T. Horie 07.03.20		
			CHECKED M. Sato 07.03.22		
			APPROVED M. Sato 07.03.22		
			RELEASED ..		
DRAWING NO. EDC3-027648-73			PART NO. HR10A-13TR-20SC(73)		
SCALE 2 : 1			CODE NO. CL110-1002-7-73		
UNITS mm			1/1		