






Mar.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.


A DETAIL OF MOUNTING GUIDE







PANEL CUTOUT (t 0.7~2)



- NOTES 1 APPLICABLE CRIMP CONTACT:HR12-SC-212(CL112-0408-9)
APPLICABLE WIRE:AWG#26 TO #30(COVERED WIRE MAX. OUTSIDE DIA.Ø1)
APPLICABLE CONTACT REMOVAL TOOL(EXTRACTION TOOL):HR12-SC-TP(CL150-0050-3)
2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. 5 TO BE 2 N·m.
LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO
PREVENT REF. NO. 5 FROM LOOSENING.

3	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0				
2	STAINLESS STEEL			5	BRASS 	NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED		4	PHOSPHOR BRONZE	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS

UNITS mm			SCALE 2 : 1		COUNT 2	DESCRIPTION OF REVISIONS DIS-C-003736	DESIGNED HR. SATO	CHECKED HY. KISHI	DATE 14. 11. 25
 HIROSE ELECTRIC CO., LTD.			APPROVED :MO. SATOH		07. 03. 13	DRAWING NO. EDC4-022885-71			
			CHECKED :EJ. KUNII		07. 03. 12	PART NO. HR10A-10R-10SC(71)			
			DESIGNED :TO. HORII		07. 03. 09	CODE NO. CL110-0606-0-71			
			DRAWN :MK. SATO		07. 03. 09	 1/1			