






May.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

B DETAIL OF MOUNTING GUIDE




PANEL CUTOUT (t 0.7~2)



- NOTES 1 APPLICABLE CRIMP CONTACT: HR10-PC-212(CL110-0514-3)
(AWG#26 TO #30; INSULATION OUTER DIA Ø1 MAX)
EXTRACTION TOOL: RP6-SC-TP(CL150-0039-0)
△ 2 THE RECOMMENDED CLAMP TORQUE OF REF.NO. ⑤ : 2N·m
LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO
PREVENT REF. NO. ⑤ FROM LOOSENING.

3	POLYBUTYLENE TEREPHTHALATE	(BLACK) UL94V-0				
2	STAINLESS STEEL			5	BRASS 	NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED		4	PHOSPHOR BRONZE	NICKEL PLATING
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS

 HIROSE ELECTRIC CO., LTD.		UNITS mm	SCALE 2 : 1		COUNT 2	DESCRIPTION OF REVISIONS DIS-C-003736	DESIGNED HR. SATO	CHECKED HY. KISHI	DATE 14. 11. 25
		APPROVED : MO. SATOH		06. 09. 13		DRAWING NO.	EDC4-025181-71		
		CHECKED : EJ. KUNII		06. 09. 11		PART NO.	HR10A-10R-12PC(71)		
		DESIGNED : TP. KOMATSU		06. 09. 07		CODE NO.	CL110-0607-2-71		
		DRAWN : TP. KOMATSU		06. 09. 07			 1/1		