


Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
 In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES
- ① APPLICABLE CRIMP TOOL, REF. NO. ⑧:HR10A-TC-02(CL150-0041-2) APPLY TO Ø5.3.
 - ② THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑥:1.5 TO 2N·m.
 - ③ ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑦:1.27.
 - ④ THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑦:0.3 TO 0.4N·m.
 - ⑤ LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ①, ⑦ FOR LOOSENING.
 - ⑥ ONE EXAMPLE OF THE ROTATION OF REF. NO. ① TO REF. NO. ⑥ IS SHOWN.
 - ⑦ THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.

4	POLYAMIDE	(BLACK) UL94V-0	9	CHLOROPRENE RUBBER	(BLACK)
3	BRASS	GOLD PLATING : 0.2µmin. NICKEL UNDER PLATING : 2µmin.	8	BRASS	
2	STAINLESS STEEL		7	STEEL	NICKEL PLATING M2.6X0.45X2
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	6	BRASS	MATTE FINISH NICKEL PLATED
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE	
HIROSE ELECTRIC CO., LTD.				APPROVED :EJ. KUNII 15.09.30 CHECKED :EJ. KUNII 15.09.30 DESIGNED :TP. KOMATSU 15.09.30 DRAWN :TP. KOMATSU 15.09.30	DRAWING NO. EDC-118515-74-74 PART NO. HR10G-7J-6P(74) CODE NO. CL110-1628-8-74			1/1