




Apr.1.2024 Copyright 2024 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.



- NOTES: ① HAND CRIMPING TOOL, REF. NO. ⑩ : HR10A-TC-02, (CL150-0041-2)
THE HOLE DIAMETER FOR CRIMPING : Ø7.0
- ② THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑥ : 2 TO 2.5N·m.
- ③ ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑨ : 1.27
THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑨ : 0.3 TO 0.4N·m.
REF. NO. ⑨ SHALL BE TIGHTENED WITH ITS TIPS PRESSED INTO
THE DIMPLE AREA OF REF. NO. ⑩
- ④ LOCTITE 263, HENKEL JAPAN OR EQUIVALENT APPLIES
TO PREVENT REF. NO. ① AND ⑨ FROM LOOSENING.
- 5 ONE EXAMPLE OF THE ROTATION OF REF. NO. ⑥ TO REF. NO. ① IS SHOWN.
- ⑥ THE ASSEMBLY THIS PRODUCT APPLIES TO THE MANUAL ETAD-C0354-00.

5	BRASS	MATTE FINISH NICKEL PLATED	10	BRASS	
4	BRASS	SILVER PLATING 2µm min.	9	STEEL	NICKEL PLATING JIS B 1177 HEXAGON SOCKET SET SCREW M2.6X0.45X3
3	BRASS		8	CR	(BLACK)
2	POLYAMIDE	(BLACK) UL94V-0	7	STEEL	NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	6	BRASS	NICKEL PLATING
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	FINISH , REMARKS
UNITS mm		SCALE 2 : 1	COUNT 2	DESCRIPTION OF REVISIONS DIS-C-00016957	
 HIROSE ELECTRIC CO., LTD.		APPROVED : MO. SATOH		20051020	DRAWING NO. EDC3-045382-73
		CHECKED : EJ. KUNII		20051020	
		DESIGNED : DS. MATSUNE		20051019	PART NO. HR10A-13P-20P(73)
		DRAWN : DS. MATSUNE		20051019	
				CODE NO. CL0110-0713-0-73	② 1/1