


1			2			3			4		
COUNT	DESCRIPTION OF REVISIONS		BY	CHKD	DATE	COUNT	DESCRIPTION OF REVISIONS		BY	CHKD	DATE
1	DIS-C-000585		T.K	E.K	07.07.27						



- NOTES 1 APPLICABLE CRIMP CONTACT:HR10-PC-212(CL110-0514-3)
APPLICABLE WIRE:AWG#26 TO #30(COVERED WIRE MAX,OUTSIDE DIA.φ 1)
APPLICABLE CONTACT REMOVAL TOOL(EXTRACTION TOOL):RP6-SC-TP(CL150-0039-0)
2 THE RECOMMENDED CLAMP TORQUE OF REF. NO. ⑤ TO BE 2N · m.
LOCTITE 242, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO
PREVENT REF. NO. ⑤ FROM LOOSENING.

3	POLYBUTYLENE TEREPHTHALATE	(BLACK)	UL94V-0	5	BRASS	NICKEL PLATING
2	STAINLESS STEEL			4	PHOSPHOR BRONZE	NICKEL PLATING
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED				
NO.	MATERIAL	FINISH, REMARKS		NO.	MATERIAL	FINISH, REMARKS
CODE NO. (OLD)			DRAWN	DESIGNED	CHECKED	APPROVED
CL			M.SATO	T.HORII	E.KUNII	M.SATO
			'07 04 11	'07 04 11	'07 04 11	'07 04 11
DRAWING NO.			PART NO.			
EDC4-042731-71			HR10G-10R-10PC(71)			
SCALE			CODE NO.			1
2 : 1			CL110-1708-5-71			1
UNITS						
mm						

HRS

HIROSE ELECTRIC CO.,LTD.

CL110-1708-5-71