




- NOTES ① APPLICABLE CRIMP TOOL, REF. NO. ⑧: HR10A-TC-02 (CL150-0041-2) APPLY TO Ø5.3.
② THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑥: 1.5 TO 2N·m.
③ ACROSS FLATS HEXAGON HEAD OF REF. NO. ⑦: 1.27.
④ THE RECOMMENDED CLAMP TORQUE, REF. NO. ⑦: 0.3 TO 0.4N·m.
⑤ LOCTITE 243, HENKEL JAPAN OR EQUIVALENT IS RECOMMENDED TO PREVENT REF. NO. ①, ⑦ FOR LOOSENING.
⑥ ONE EXAMPLE OF THE ROTATION OF REF. NO. ① TO REF. NO. ⑥ IS SHOWN.
⑦ THE CABLE PULL AND TWISTING STRENGTH AND OTHER CHARACTERISTICS MAY DIFFER, DEPENDING ON THE CABLE STRUCTURE. PLEASE CONFIRM BEFORE THE USE.

			9	CHLOROPRENE RUBBER	(BLACK)
4	POLYAMIDE	(BLACK) UL94V-0	8	BRASS	
3	BRASS	SILVER PLATING : 2μmin.	7	STEEL	NICKEL PLATING M2. 6X0.45X2
2	STAINLESS STEEL		6	BRASS	MATTE FINISH NICKEL PLATED
1	ZINC ALLOY	MATTE FINISH NICKEL PLATED	5	BRASS	MATTE FINISH NICKEL PLATED
NO.	MATERIAL	FINISH . REMARKS	NO.	MATERIAL	FINISH . REMARKS

UNITS mm		SCALE 2 : 1	COUNT 	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
APPROVED : EJ. KUNII 15.09.30				DRAWING NO. EDC-042715-73-73			
CHECKED : EJ. KUNII 15.09.30				PART NO. HR10G-7J-4P(73)			
DESIGNED : TP. KOMATSU 15.09.30				CODE NO. CL110-1612-8-73			
DRAWN : TP. KOMATSU 15.09.30							