

APPLICABLE STANDARD					
RATING	OPERATING TEMPERATURE RANGE	-10 °C TO +60 °C	STORAGE TEMPERATURE RANGE	-10 °C TO +60 °C	
	VOLTAGE	AC 30 V , DC 40 V			
	CURRENT	2 A	APPLICABLE CABLE		
SPECIFICATIONS					
ITEM		TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION					
GENERAL EXAMINATION		VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	X	X
MARKING		CONFIRMED VISUALLY.		X	X
ELECTRIC CHARACTERISTICS					
CONTACT RESISTANCE		CONTACT SHALL BE MEASURED AT DC 1 A	30 mΩ MAX.	X	—
INSULATION RESISTANCE		250 V DC.	1000 MΩ MIN.	X	X
VOLTAGE PROOF		300 V AC. FOR 1 min.	NO FLASHOVER OR BREAKDOWN.	X	X
MECHANICAL CHARACTERISTICS					
CONTACT INSERTION AND WITHDRAWAL FORCES		— BY STEEL GAUGE.	INSERTION AND WITHDRAWAL FORCES : — N MIN.	—	—
CONNECTOR INSERTION AND WITHDRAWAL FORCES		MEASURED BY APPLICABLE CONNECTOR.	INSERTION AND WITHDRAWAL FORCES LOCKING DEVICE WITH UNLOCK : — N MAX. LOCKING DEVICE WITH LOCK : 70 N MAX.	X	—
MECHANICAL OPERATION		1000 TIMES INSERTIONS AND EXTRACTIONS.	CONTACT RESISTANCE: 45 mΩ MAX.	X	—
VIBRATION		FREQUENCY: 10 TO 55 Hz, SINGLE AMPLITUDE 0.75 mm, — m/s ² AT 2h, FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	—
SHOCK		490 m/s ² DIRECTIONS OF PULSE 11 ms AT 3 TIMES FOR 3 DIRECTIONS.	① NO ELECTRICAL DISCONTINUITY OF 10 μs. ② NO DAMAGE, CRACK AND LOOSENESS, OF PARTS.	X	—
ENVIRONMENTAL CHARACTERISTICS					
DAMP HEAT (STEADY STATE)		EXPOSED AT 40 °C, 90 TO 95 %, 96 h.	① INSULATION RESISTANCE: 10 MΩ MIN (AT HIGH HUMIDITY). ② INSULATION RESISTANCE: 100 MΩ MIN (AT DRY). ③ NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
RAPID CHANGE OF TEMPERATURE		TEMPERATURE -55 → R/T ⁽¹⁾ → +85 → R/T °C TIME 30 → 10 TO 15 → 30 → 10 TO 15 min UNDER 5 CYCLES.	① INSULATION RESISTANCE: 500 MΩ MIN.. ② NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
CORROSION SALT MIST		EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	NO HEAVY CORROSION RUIN THE FUNCTION.	X	—
DRY HEAT		EXPOSED AT + 85 °C , 96 h.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
COLD		EXPOSED AT - 55 °C , 96 h.	NO DAMAGE, CRACK AND LOOSENESS OF PARTS.	X	—
RESISTANCE TO SOLDERING HEAT		NO PHYSICAL OF ELECTRICAL DAMAGE AFTER CONTACT IMMERSION IN THE SOLDER BATH OF 260 °C ± 5 °C FOR 10 SEC NO DEFECTS AS MELTING.		X	—
LOCK STRENGTH		CONNECTOR MUST NOT REMOVE AT THE VALUE BELOW STD. VALUE	50 N MIN.	—	—
	COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
	3	DIS-C-001413	TY. SUZUKI	HY. KISHI	09. 09. 16
REMARK NOTE (1) R/T : ROOM TEMPERATURE Unless otherwise specified, refer to JIS C 5402.			APPROVED	MR. YOSHIDA	05. 01. 05
			CHECKED	MO. SATOH	05. 01. 05
			DESIGNED	YH. YAMADA	05. 01. 05
			DRAWN	YH. YAMADA	05. 01. 05
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			DRAWING NO.		ELC4-021589-00
	SPECIFICATION SHEET		PART NO.	RP13A-12RC-20PB	
	HIROSE ELECTRIC CO., LTD.		CODE NO.	CL113-0211-0-00	1/1