

Nov.1.2021 Copyright 2021 HIROSE ELECTRIC CO., LTD. All Rights Reserved.
In case of consideration for using Automotive equipment / device which demand high reliability, kindly contact our sales window correspondents.

APPLICABLE STANDARD				
RATING	OPERATING TEMPERATURE RANGE	— °C TO — °C	STORAGE TEMPERATURE RANGE	— °C TO — °C
	VOLTAGE	AC — V , DC — V		
	CURRENT	2 A (WHEN USING APPLICABLE WIRE AWG#24)	APPLICABLE CABLE	AWG#30 ~ #24 (INSULATION DIA. 1.15 MAX)
SPECIFICATIONS				
ITEM	TEST METHOD	REQUIREMENTS	QT	AT
CONSTRUCTION				
GENERAL EXAMINATION	VISUALLY AND BY MEASURING INSTRUMENT.	ACCORDING TO DRAWING.	×	×
MARKING	CONFIRMED VISUALLY.		×	×
ELECTRIC CHARACTERISTICS				
CONTACT RESISTANCE UNIT CONTACT	CONTACT SHALL BE MEASURED AT DC 1 A.	15 mΩ MAX.	×	—
MECHANICAL CHARACTERISTICS				
MECHANICAL OPERATION	1000 TIMES INSERTIONS AND EXTRACTIONS.	CONTACT RESISTANCE: 20 mΩ MAX.	×	—
TENSIL STRENGTH (CRIMPED CONNECTION)	CRIMPED ONLY CONDUCTOR OF THE APPLICABLE WIRE AND PULLING THE APPLICABLE WIRE.	<ul style="list-style-type: none"> • AWG#30 : 10 N MIN. • AWG#28 : 16 N MIN. • AWG#26 : 24 N MIN. • AWG#24 : 36 N MIN. 	×	—
ENVIRONMENTAL CHARACTERISTICS				
CORROSION SALT MIST	EXPOSED IN 5 % SALT WATER SPRAY FOR 48 h.	NO HEAVY CORROSION RUIN THE FUNCTION.	×	—
COUNT	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
0				
REMARK		APPROVED	SU. OBARA	11. 01. 24
		CHECKED	HY. KISHI	11. 01. 21
		DESIGNED	TH. KAMEYA	11. 01. 21
		DRAWN	YS. SAKODA	09. 11. 06
Unless otherwise specified, refer to JIS C 5402.				
Note QT:Qualification Test AT:Assurance Test X:Applicable Test		DRAWING NO.	ELC4-021030-00	
HRS	SPECIFICATION SHEET	PART NO.	RP19-PC-222	
	HIROSE ELECTRIC CO., LTD.	CODE NO.	CL113-0264-7-00	△ 1/1